# **Bandpass Filter**

**VBF-1525+** 

50Ω 1480 to 1570 MHz

# **The Big Deal**

- Low Insertion Loss (2.0 dB typical)
- Good close-in rejection
- Versatile small size, coaxial, 1.43" length



CASE STYLE: FF704

## **Product Overview**

The VBF-1525+ Band Pass Filter is constructed using internal LTCC Band Pass Filter structure to achieve repeatable performance. Covering 1525 MHz  $\pm$  45 MHz, these units offer low insertion loss and good rejection at the band reject edges. Built using Mini-Circuits proven unibody construction which integrates the RF connectors with the case body, the VBF-1525+ takes very little space and meets rugged test lab system environment.

# **Key Features**

Feature	Advantages
Good Rejection close to pass band	Provides good rejection of signals close to the pass band, for improved system performance.
Compact Versatile Case (1.43"x0.41")	Enables use in a variety of applications including space constrained connectorized systems.  Connectors: SMA Female (1), SMA Male (1)
Rugged Unibody Construction	Mini-Circuits Unibody construction allows survivability in critical applications including militarized or industrial systems.

#### Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.ninicircuits.com/MCLStore/terms.jsp

# **Bandpass Filter**

#### $50\Omega$ 1480 to 1570 MHz

#### **Maximum Ratings**

Operating Temperature	-55°C to 100°C		
Storage Temperature	-55°C to 100°C		
RF Power Input*	1.5W max_at 25°C		

<sup>\*</sup>Passband rating, derate linearly to 0.25W at 100°C ambient Permanent damage may occur if any of these limits are exceeded.

# **Features**

- · Small size
- Temperature stable
- · Rugged unibody construction

VBF-1525+

CASE STYLE: FF704

Connectors	Model
SMA	VBF-1525+


#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

# **Applications**

- Harmonic Rejection
- Transmitters / Receivers


### **Outline Drawing**




## Electrical Specifications at 25°C

Parar	neter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	_	_	_	1525	_	MHz
Pass Band	Insertion Loss	F1-F2	1480-1570	_	_	3.0	dB
	VSWR	F1-F2	1480-1570	_	_	2.5	:1
Oten Dend Leven	Insertion Loss	DC-F3	DC-1150	_	20	_	dB
Stop Band, Lower	VSWR	DC-F3	DC-1150	_	25	_	:1
Stop Band, Upper	Insertion Loss	F4-F5	2900-5100	_	25	_	dB
Stop Ballu, Oppel	VSWR	F4-F5	2900-5100	_	20	_	:1

#### **Typical Frequency Response**



#### **Functional Schematic**





### Outline Dimensions (inch mm)


	Е	D	В
gra	.312	1.43	.410
1	7.92	36.32	10.41

#### Typical Performance Data at 25°C

Insertion Loss (dB)	VSWR (:1)		
65.45	2271.75		
36.71	110.05		
37.14	65.76		
49.26	51.32		
40.11	45.74		
17.00	18.94		
2.80	1.73		
2.32	1.98		
2.00	1.13		
18.50	47.88		
24.10	65.44		
27.40	71.84		
34.81	71.10		
58.38	63.85		
32.14	30.99		
	(dB)  65.45 36.71 37.14 49.26 40.11 17.00 2.80 2.32 2.00 18.50 24.10 27.40 34.81 58.38		







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

  B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

  C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp