Bandpass Filter

VBFZ-2130-S+

2000 to 2260 MHz 50Ω

Maximum Ratings

Operating Temperature	-55°C to 100°C		
Storage Temperature	-55°C to 100°C		
RF Power Input*	7W at 25°C		

^{*}Passband rating, derate linearly to 3W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.

Features

- · Good Rejection, 30dB up to 18GHz
- Low insertion loss
- Excellent power handling, 7W
- Temperature stable LTCC internal structure
- · Rugged stainless steel unibody
- Protected by US Patent 6,943,646

Applications

- Harmonic rejection
- Transmitters/receivers
- Lab use
- Test instrumentation

Generic photo used for illustration purposes only


CASE STYLE: FF1145

Connectors Model VBFZ-2130-S+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing



Outline Dimensions (inch)

Note: Please refer to case style drawing for details

1.91

48.51

.410

10.41

Ε

.312

7.92

wt.


grams

11.8


Bandpass Filter Electrical Specifications (T_{AMB}= 25°C)

CENTER FREQ.	PASSBAND (MHz)	STOPBANDS (MHz)		lHz)	VSWR (:1)			
(MHz)	(Loss < 2.6dB)	(Loss >	20dB)	(Loss	30dB Typ)	Pass	band	Stopband
Fc	F1 - F2	F3	F4	F5	F6	Тур.	Max.	Тур.
2130	2000 - 2260	1420	2950	1400	2950 - 18000	1.6	2.8	20

Typical Frequency Response



Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)		
50	79.71	9101.03		
500	80.20	421.71		
1010	59.20	108.86		
1400	35.53	39.85		
1420	33.32	36.94		
1605	14.83	13.49		
1684	7.90	5.68		
1753	3.93	2.43		
2000	1.92	1.74		
2130	1.88	1.72		
2260	1.76	1.32		
2540	3.39	1.76		
2635	6.41	1.75		
2710	13.61	3.83		
2795	25.49	7.28		
2840	32.11	8.65		
2950	39.28	9.32		
7000	45.16	38.06		
10000	44.11	5.21		
18000	34.85	1.59		

VBFZ-2130-S+ INSERTION LOSS 90 80 NSERTION LOSS(dB) 70 60 50 40 30 20 10

VBFZ-2130-S+ VSWR 1000 VSWR 100 10

4500

0

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

FREQUENCY (MHz)

13500

18000