

Engineering Development Model

RF Transformer

TCM4-ED12216/1

Impedance Ratio : 4

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



CASE STYLE : DB714

Please click "Back", and then click "Contact Us" for Applications support.


ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	2		2400	MHz
Insertion Loss *	3 dB Bandwidth		2 - 2400	MHz
	2 dB Bandwidth		2 - 1200	MHz
	1 dB Bandwidth		4 - 700	MHz

Notes:

* Insertion Loss is referenced to mid-band loss, 0.89dB typ.

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25 W
DC Current	30 mA

Configuration :H



PIN CONNECTIONS	
PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	1
SECONDARY	3
SECONDARY CT	2
NOT USED	5

