1400 to 5000 MHz

Maximum Ratings

 50Ω

Operating Temperature	-55°C to 100°C		
Storage Temperature	-55°C to 100°C		
DE Dower Input*	7W may at 25°C		

^{*} Passband rating, derate linearly to 3W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.

Features

- rugged unibody construction, small size
- 7 sections
- temperature stable

Applications sub-harmonic rejection • transmitters/receivers

· excellent power handling, 7W

- low cost

lab use

Generic photo used for illustration purposes only CASE STYLE: FF704


VHF-1300+

Connectors Model VHF-1300+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing




Outline Dimensions (inch)

wt	E	D	В
grams	.312	1.43	.410
10.0	7 92	36.32	10 41


Electrical Specifications (T_{AMB}=25°C)

STOP BAND (MHz) Min.		fco, MHz Nom.	PASSBAND (MHz)		VSWR (:1) Typ.		NO. OF SECTIONS
IMI	in.	(loss 3 dB)	(loss < 1.3 dB)	(loss < 2 dB)		Frequency (MHz)	
(loss > 40 dB)	(loss > 20 dB)	Тур.	Max.	Typ.	Stopband	1.5:1	
680	930	1300	1510-4000	1400-5000	20:1	1400-4000	7

typical frequency response





electrical schematic



Typical Performance Data

	(:1)
89.20	868.59
73.46	868.59
45.52	78.97
27.34	39.49
13.31	17.05
6.74	6.91
3.40	3.29
1.42	1.58
1.01	1.36
0.64	1.31
0.59	1.47
0.43	1.29
0.49	1.42
1.48	2.73
4.52	7.47
	73.46 45.52 27.34 13.31 6.74 3.40 1.42 1.01 0.64 0.59 0.43 0.49 1.48





A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp