High Pass Filter

VHF-1320+

50Ω 1700 to 5000 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	7W max. at 25°C

^{*} Passband rating, derate linearly to 3W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded

Features

- rugged unibody construction, small size
- 7 sections
- temperature stable

Applications sub-harmonic rejection • transmitters/receivers

- · excellent power handling, 7W
- low cost

lab use

Generic photo used for illustration purposes only


CASE STYLE: FF704

Connectors Model VHF-1320+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing




Outline Dimensions (inch)

В D Е wt .410 1.43 .312 grams 10.41 36.32 7.92 10.0


Electrical Specifications (T_{AMB}=25°C)

,	Hz)	fco, MHz Nom.	PASSBAND (MHz)		VSWR (:1) Typ.		NO. OF SECTIONS
M	in.	(loss 3 dB)	(loss < 1.3 dB)	(loss < 2 dB)		Frequency (MHz)	
(loss > 40 dB)	(loss > 20 dB)	Тур.	Max.	Typ.	Stopband	1.5:1	
880	1060	1320	1700-3800	1400-5000	20:1	1700-3700	7

typical frequency response




electrical schematic



Typical Performance Data

Insertion Loss (dB)	VSWR (:1)
94.16	1737.18
	434.30
	52.65
26.59	27.16
13.65	12.01
6.27	4.50
2.92	2.07
1.55	1.43
0.76	1.31
0.52	1.55
0.62	1.65
	3.25
	4.89
	8.43
	94.16 69.22 51.00 26.59 13.65 6.27 2.92 1.55 0.76





A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp