Coaxial **Low Pass Filter**

50O

*DC to 400 MHz

Maximum Ratings

0	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	8.5W max. at 25°C

* Passband rating, derate linearly to 3.5W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.

Features

- rugged uni-body construction, small size
- 7 sections
- excellent power handling, 8.5W
- temperature stable
- low cost
- protected by U.S. Patent 6,943,646

Applications

Max

- harmonic rejection
- transmitters/receivers
- lab use




CASE STYLE: FF704

Connectors Model SMA VLF-400+

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site

for RoHS Compliance methodologies and qualifications

Outline Drawing



Outline Dimensions (inch)

В	D	Е	wt
.410	1.43	.312	grams
10.41	36.32	7.92	10.0

Electrical Specifications at 25°C PASSBAND STOP BAND (MHz) fco, MHz VSWR NO. OF SECTIONS (MHz) Nom. (loss, dB) (:1) (loss < 1 dB)(loss 3 dB) f 20 40 fr 20 Stopband Passband

Тур

5500

Тур.

20


Тур

Тур. *DC-400 560 680-3000 660

Min

* Not for use with DC voltage at input and output ports

typical frequency response




electrical schematic

Тур


1.2


7



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1	0.06	1.02
100	0.27	1.10
400	0.80	1.12
500	1.44	1.39
560	2.77	2.01
600	5.87	3.54
620	9.82	5.72
650	20.09	10.62
660	24.64	12.01
680	35.49	14.50
1000	42.32	33.42
2000	59.01	57.91
3000	39.73	64.35
4500	23.58	45.72
5500	23.21	43.44





VSWR

Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp

