Plug-In **RF Transformer** 0.3 to 120 MHz **50**Ω

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	0.25W
DC Current	30mA
	4 H H H

Permanent damage may occur if any of these limits are exceeded.

Pin Connections


PRIMARY DOT	1
PRIMARY	5
SECONDARY DOT	2
SECONDARY	6
SECONDARY CT	4
CASE GROUND	7, 8
NOT USED	3

Outline Drawing



Outline	Dimensions	$\binom{inch}{mm}$
---------	------------	--------------------

А	В	С	D	E	F
.480	.500	.240	.255	.210	.230
12.19	12.70	6.10	6.48	5.33	5.84
G	Н	J	K		wt
.100	.20	.14	.020		grams
2.54	5.08	3.56	0.51		1.9



Features

• excellent return loss • hermetic case

Applications

- military, hi-rel requirements
- impedance matching





CASE STYLE: A11

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Transformer Electrical Specifications

Ω RATIO (Secondary/Primary)	FREQUENCY (MHz)	INSERTION LOSS*		
		3 dB MHz	2 dB MHz	1 dB MHz
13	0.3-120	0.3-120	0.7-80	5-20

*Insertion Loss is referenced to mid-band loss, 0.7 dB typ.

Typical Performance Data

//			
FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	
0.30	2.63	6.95	
1.01	1.59	11.16	
2.17	1.14	13.24	
10.03	0.76	14.21	
20.13	0.81	11.28	
45.28	0.97	6.32	
46.55	0.98	6.21	
100.51	1.65	2.51	
108.53	1.77	2.25	
120.00	1.92	1.97	



Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp

Mini-Circuits

REV. C M151107 TMO-13-1T+ IG/TD/AM 151008 Page 1 of 1