VLFG-3500+

 50Ω DC to 3500 MHz

Generic photo used for illustration purposes only CASE STYLE: FF704

The Big Deal

- Excellent power handling, 4.5W
- Temperature stable
- Rugged unibody construction
- Good rejection, 40 dB typical

Product Overview

VLFG-3500+ is a 50Ω low pass filter built in rugged unibody construction. Covering DC-3500 MHz bandwidth, these units offer good matching within the passband and good rejection in stopband. VLFG-3500+ offer low insertion loss, and excellent power handling capability. It handles up to 4.5W RF input power and provides a wide operating temperature range from -55°C to 125°C.

Key Features

Feature	Advantages		
Low passband insertion loss	Suitable for high performance application.		
4.5W Power handling	Supports a range of system power requirements.		
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.		

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Low Pass Filter

DC to 3500 MHz 50Ω

VLFG-3500+



Generic photo used for illustration purposes only CASE STYLE: FF704

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Features

- Low loss, 1.3 dB typical
- · Good rejection 40 dB typical
- · Excellent power handling, 4.5W
- Temperature stable
- Connectorized package
- Rugged unibody construction


Applications

- · Military radar applications
- Test and measurement
- · Telecommunication and broadband wireless applications

Functional Schematic



Typical Frequency Response



Electrical Specifications at 25°C

· · · · · · · · · · · · · · · · · · ·							
Pa	rameter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Insertion Loss	DC-F1	DC - 3500	_	1.3	2.2	dB
Pass Band	Freq. Cut-Off	F2*	3970	_	3.0	_	dB
	Return Loss	DC-F1	DC - 3500	_	14	_	dB
		F3-F4	4800 - 5000	20	35	_	dB
Stop Band	Rejection Loss	F4-F5	5000 - 8500	30	38	_	dB
		F5-F6	8500 - 15000	_	25		dB

In Application where DC voltage is present at either input or output port. DC blocks are required.


^{*} Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.


Maximum Ratings			
Operating Temperature	-55°C to 125°C		
Storage Temperature	-55°C to 125°C		
RF Power Input*	4.5W max.@25°C		


^{*}Passband rating, derate linearly to 1W at 125°C ambient Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

10 0.05 41.80 100 0.10 37.37 1000 0.32 30.03 1400 0.41 23.93 1800 0.51 20.20 3000 0.88 22.19 3500 1.22 27.04 3970 2.49 13.34 4100 3.89 8.18
1000 0.32 30.03 1400 0.41 23.93 1800 0.51 20.20 3000 0.88 22.19 3500 1.22 27.04 3970 2.49 13.34
1400 0.41 23.93 1800 0.51 20.20 3000 0.88 22.19 3500 1.22 27.04 3970 2.49 13.34
1800 0.51 20.20 3000 0.88 22.19 3500 1.22 27.04 3970 2.49 13.34
3000 0.88 22.19 3500 1.22 27.04 3970 2.49 13.34
3500 1.22 27.04 3970 2.49 13.34
3970 2.49 13.34
1 4100 9.00 9.10
1 4100 5.09 6.16
4500 18.91 1.75
4800 42.15 1.15
5000 53.59 1.00
6000 56.36 0.70
7000 50.22 0.60
8500 40.62 0.46
10000 36.21 0.40
11000 34.11 0.47
12000 33.37 0.64
13000 29.00 0.89
15000 28.16 1.08







Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Coaxial Connections

PORT - 1	SMA-Male
PORT - 2	SMA-Female

Outline Drawing



Outline Dimensions (inch)

wt	Ε	D	В
grams	.312	1.43	.410
10	7 92	36.32	10 41

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Firms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

