RF Transformer

0.2 to 350 MHz

TMO-4-1+



CASE STYLE: A11

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Maximum Ratings

Operating Temperature	-55°C to 100°C	
Storage Temperature	-55°C to 100°C	
RF Power	0.25W	
DC Current	30mA	
Permanent damage may occur if any	of these limits are exceeded.	

Pin Connections

PRIMARY DOT	1
PRIMARY	5
SECONDARY DOT	2
SECONDARY	6
SECONDARY CT	4
CASE GROUND	7, 8
NOT USED	3


Outline Drawing



Outline Dimensions (inch)

-	E	D	C	В	Α
.230	.210	.255	.240	.500	.480
5.84	5.33	6.48	6.10	12.70	12.19
wt		K	J	Н	G
grams		.020	.14	.20	.100
1.9		0.51	3.56	5.08	2.54

Config. A



- hermetic case

Features • excellent return loss

Applications

- military, hi-rel requirements
- impedance matching


Transformer Electrical Specifications


Ω RATIO (Secondary/Primary)	FREQUENCY (MHz)	INSERTION LOSS*		
		3 dB MHz	2 dB MHz	1 dB MHz
4	0.2-350	0.2-350	0.35-300	2-100

^{*}Insertion Loss is referenced to mid-band loss, 0.5 dB typ.

Typical Performance Data

FREQU (MH		R. LOSS	
0.2	20 2.20	7.00	
0.6	51 1.19	13.99	
1.2	27 1.00	16.82	
5.0	0.61	22.86	
10.0	0.56	24.46	
22.5	53 0.58	22.32	
45.8	33 0.60	17.98	
100.8	37 0.70	11.84	
193.0	38 0.86	6.33	
350.0	00 1.04	2.27	





- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp