ow Pass Filter

VLFX-1050+

DC to 1050 MHz 50Ω

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	10W max. at 25°C
ni rowei iliput	1000 Illax. at 25 C

*Passband rating, derate linearly to 3.5W at 100°C ambient.

Permanent damage may occur if any of these limits are exceeded.

Features

- 21 sections
- excellent power handling, 10W
- temperature stable LTCC internal structure
- re-entry frequency > 20 GHz
- rugged unibody construction
- protected by US patent 6,943,646

Applications

- · harmonic rejection
- · transmitters/receivers
- lab use
- · test instrumentation


CASE STYLE: FF1118

Model SMA VLFX-1050+ SMA VLFX-1050

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing



Outline Dimensions (inch)


wt.	Е	D	В
grams	.312	2.67	.410
17.0	7 92	67.82	10.41


Low Pass Filter Electrical Specifications @ 25°C

MODEL NO.	PASSBAND (MHz) DC-F1	MHz Nom. F2 (Loss 3 dB)	STOPBAND (MHz) F3-F4 (Loss, dB)		VSWR (:1)		NO. OF SECTIONS
	(Loss < 1.7dB) Max.	Тур.	20 Min.	30 Typ.	Stopband Typ.	Passband Typ.	
VLFX-1050 (+)	DC-1050	1675	2050	0-20000	10	1.9	21

Typical Frequency Response


Functional Schematic






Typical Performance Data @ 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50	0.12	1.03
400	0.39	1.14
1050	1.07	1.64
1450	1.47	1.33
1675	3.62	2.07
1750	7.40	3.99
1850	16.91	8.55
1900	22.89	10.89
1950	29.24	12.89
2000	35.21	14.74
2050	39.55	16.41
2100	40.09	17.93
3000	58.99	34.07
4000	85.99	34.07
6000	77.27	40.41
8000	74.19	32.79
10000	63.43	34.75
14000	47.23	12.89
16000	65.79	22.29
20000	54.93	6.56





- Notes
 A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp