

Plug-In RF Transformer

75Ω 10 to 500 MHz

TO-75+



Generic photo used for illustration purposes only

CASE STYLE: PP94

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	250mW
DC Current	30mA

Pin Connections

PRIMARY DOT	1
PRIMARY	2
SECONDARY DOT	4
SECONDARY	3

Features

- wideband, 10 to 500 MHz
- hermetic metal case

Applications


- balanced to unbalanced transformation
- impedance matching
- military, hi-rel application

Transformer Electrical Specifications

Ω RATIO	FREQUENCY (MHz)	INSERTION LOSS*		
		3 dB MHz	2 dB MHz	1 dB MHz
1	10-500	—	10-500	40-250

* Insertion Loss is referenced to mid-band loss, 0.5 dB typ.

Outline Drawing






Outline Dimensions (inch/mm)

A	B	C	D
.360	.250	.25	.016
9.14	6.35	6.35	0.41
E	F	G	wt
.020	.04	.200	grams
0.51	1.02	5.08	1.5

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)
10.00	0.53	24.68
14.89	0.53	25.54
24.87	0.56	26.08
49.60	0.59	26.40
100.87	0.69	25.11
193.38	0.76	22.22
298.43	0.83	19.48
401.16	0.89	17.42
451.55	0.90	16.74
500.00	0.90	16.24

Config. C



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

