

Low Pass Filter

50Ω DC to 1300 MHz (40 dB Isolation up to 20 GHz)

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

RF Power Input* 10W max. at 25°C

*Passband rating, derate linearly to 3.5W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.


Features

- very good isolation, 40 dB up to 20 GHz
- 21 sections
- excellent power handling, 10W
- temperature stable LTCC internal structure
- re-entry frequency > 20 GHz
- rugged unibody construction
- protected by US patent 6,943,646

Applications

- harmonic rejection
- transmitters/receivers
- lab use
- test instrumentation

VLFX-1300




CASE STYLE: FF1118

Connectors	Model
SMA	VLFX-1300

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing




Outline Dimensions (inch mm)

B	D	E	wt.
.410	2.67	.312	grams
10.41	67.82	7.92	17.0


Low Pass Filter Electrical Specifications @ 25°C

MODEL NO.	PASSBAND (MHz)	Fco, MHz Nom	STOPBAND (MHz) (Loss, dB)		VSWR (:1)		NO. OF SECTIONS
	(Loss < 1.2dB) Max.	(Loss 3 dB) Typ	F20 Min.	F40 Typ.	Stopband Typ.	Passband Typ.	
VLFX-1300	DC-1300	1925	2300	2500-20000	10	1.2	21

Typical Frequency Response





Functional Schematic



Typical Performance Data @ 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50	0.21	1.05
300	0.34	1.09
600	0.46	1.11
1300	0.95	1.18
1600	1.27	1.10
1750	1.58	1.20
1850	2.14	1.56
1925	3.07	2.15
2100	9.35	6.43
2300	33.88	15.28
2500	55.25	17.62
3000	68.08	23.79
4000	81.32	47.72
5000	72.73	76.04
7500	53.99	20.63
10000	72.31	69.62
12500	65.95	6.98
15000	64.17	2.10
17500	75.05	31.26
20000	70.82	5.83



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

