Frequency Mixer

TUF-2HSM+

Level 17 (LO Power +17 dBm) 50 to 1000 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA


Permanent damage may occur if any of these limits are exceeded

Pin Connections

LO	4
RF	1
IF	2
GROUND	3
CASE GROUND	3

Outline Drawing






Suggested Layout,

Outline Dimensions (inch)

Α	В	С	D	Е	F	G
.50	.48	.255	.240	.23	.21	.06
12.70	12.19	6.48	6.10	5.84	5.33	1.52
Н	J	K	L	M	N	wt
H .100	J .09	.16	.020	M .09		wt grams

Demo Board MCL PIN: TB-201 Suggested PCB Layout (PL-081)



NOTES: 1.TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030° ± 0.002°; COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2.BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- low conversion loss, 6.20 dB typ.
- excellent L-R isolation, 47 dB typ.; L-I, 44 dB typ.
- good IP3, 21 dBm typ.
- rugged welded construction

Applications

- VHF/UHF
- cellular
- ISM/GSM

Generic photo used for illustration purposes only CASE STYLE: NNN150

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

	UENCY Hz)	CON		SION dB)	LOSS	LO-RF ISOLATION (dB)				LO-IF ISOLATION (dB)					IP3 @ CENTER BAND (dBm)			
LO/RF	IF	N	1id-Bar m	nd	Total Range		L	ı	M	ι	J	ı	L	N	Л	ι	J	
f _L -f _U		X	σ	Max.	Max.	Тур.	Min.	Тур.	Min.	Тур.	Min.	Тур.	Min.	Тур.	Min.	Тур.	Min.	Тур.
50-1000	DC-1000	6.20	0.22	7.5	9.0	58	40	47	30	42	25	58	35	44	25	28	18	21

1 dB COMP.: +14 dBm typ.


L = 50-100 MHz M = 100-500 MHz $U = \text{upper range } [f_{ij}/2 \text{ to } f_{ij}]$

m= mid band $[2f_i \text{ to } f_i/2]$

Typical Performance Data

Freque (MH	ency z)	Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)	
RF	RF LO		LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm	
5.00 35.15 65.30 125.61 185.91 216.06 276.37 336.67 396.98 457.28 517.58 547.74 608.04	35.00 65.15 95.30 95.61 155.91 186.06 246.37 306.67 366.98 427.28 487.58 517.74 578.04	+17dBm 5.75 5.78 5.83 5.88 5.87 5.70 5.62 5.78 6.15 5.88 5.91 6.36	73.03 53.95 47.75 45.94 41.73 40.07 37.49 35.70 35.50 33.92 34.70 35.38 34.75	64.57 50.91 44.94 42.85 38.74 37.26 34.59 32.97 32.29 30.55 29.07 29.45 28.29	1.24 1.10 1.10 1.09 1.09 1.10 1.11 1.11 1.12 1.13 1.15 1.15	1.51 1.53 1.52 1.44 1.43 1.39 1.38 1.40 1.37 1.36	
668.34 728.65	638.34 698.65	6.50 6.30	34.53 33.69	27.06 25.41	1.17 1.20	1.38 1.36	
788.95 849.26 909.56 969.86 1000.00	758.95 819.26 879.56 939.86 970.00	6.43 7.56 8.59 8.55 8.57	32.39 32.23 32.46 32.66 32.20	25.21 24.28 23.91 24.30 24.05	1.22 1.26 1.34 1.46 1.62	1.45 1.49 1.52 1.54 1.53	


Electrical Schematic





- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


 C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp














Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits stapilicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/WCLStore/terms.jsp