# Plug-In **Frequency Mixer**

# Level 7 (LO Power + 7 dBm) 0.15 to 400 MHz


#### **Maximum Ratings**

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA
Permanent damage may occur if any	of these limits are exceeded

#### **Pin Connections**

LO	4
RF	1
IF	2
GROUND	3
CASE GROUND	3

#### **Outline Drawing**



A B C D E F   .480 .500 .240 .255 .210 .230   12.19 12.70 6.10 6.48 5.33 5.84										
Α	В	С	D	E	F					
.480	.500	.240	.255	.210	.230					
12.19	12.70	6.10	6.48	5.33	5.84					
G	н	J	K	L	wt					
.16	.100	.14	.20	.020	grams					
4.06	2.54	3.56	5.08	0.51	1.9					

#### **Features**

- low conversion loss, 4.7 dB typ.
- high isolation, 46 dB typ. L-R, 47 dB typ. L-I
- rugged welded construction

#### **Applications**

#### • HF/VHF

• defense & federal communications



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### **Electrical Specifications**


FREQU (MI	JENCY Hz)	COI		SION dB)	LOSS	LO-RF ISOLATION (dB)				LO-IF ISOLATION (dB)					IP3 @ CENTER BAND (dBm)			
LO/RF f <sub>L</sub> -f <sub>u</sub>	IF	N   <u>X</u>	/lid-Bar m σ	nd Max.	Total Range Max.			N Typ.	vi Min.	U Typ. Min.		L Typ. Min.		M Typ. Min.		U Tvp. Min.		Тур.
0.15-400	DC-400	4.7	0.02	7.0	8.0	60	50	46	30	35	25	60	40	47	25	35	20	11
1 dB COMP.: +1 dBm typ. For phase detection, DC positive polarity					L = low range $[f_L \text{ to } 10 f_L]$ M = m m= mid band $[2f_L \text{ to } f_U/2]$					mid range [10 $f_L$ to $f_U/2$ ] U = upper				range $[f_U/2 \text{ to } f_U]$				

with in-phase RF & LO.

#### **Typical Performance Data**

	luency (Hz)	Conversion Loss (dB)	VSWR RF Port (:1)	Frequency (MHz)	lsolation L-R (dB)	lsolation L-I (dB)	VSWR LO Port (:1)				
RF	LO	LO +7dBm	LO +7dBm	LO	LO +7dBm	LO +7dBm	LO +7dBm				
0.15 0.23 0.30 0.50 1.00 2.80 6.40 10.00 28.00 64.00 100.00 138.00 157.00 195.00 233.00 252.00 271.00	30.15 30.23 30.30 31.00 32.80 36.40 40.00 58.00 94.00 130.00 168.00 187.00 225.00 263.00 282.00 301.00	5.37 5.27 5.21 5.16 5.08 4.91 4.91 4.73 4.71 4.75 4.83 4.85 4.83 4.85 4.83 4.92 4.97 5.10 5.10 5.10 5.10	1.57 1.41 1.33 1.25 1.21 1.21 1.21 1.21 1.21 1.21 1.21	10.00 20.00 30.00 40.00 76.00 94.00 112.00 149.00 168.00 206.00 225.00 244.00 282.00 301.00 320.00 340.00 360.00	$\begin{array}{c} 68.68\\ 65.36\\ 63.22\\ 61.75\\ 57.56\\ 56.48\\ 54.90\\ 52.63\\ 54.13\\ 49.62\\ 48.10\\ 48.03\\ 53.65\\ 55.10\\ 54.03\\ 52.86\\ 51.53\\ \end{array}$	61.84 56.87 54.20 52.09 47.59 45.97 44.70 42.36 42.02 38.81 38.56 37.82 37.79 38.07 37.59 36.62 35.44	2.59 2.60 2.59 2.58 2.54 2.50 2.50 2.57 2.55 2.62 2.66 2.68 2.68 2.67 2.76 2.82 2.76 2.69				
290.00 370.00 400.00	320.00 340.00 370.00	5.15 5.38 5.41	1.17 1.10 1.05	390.00 410.00 430.00	47.44 45.39 44.42	33.11 32.24 32.17	2.86 3.05 3.06				

#### **Electrical Schematic**



A. Performance and quality attributes and conditions of expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Nlin-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Nlini-Circuit standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

REV. B M151107 TUF-3+ DJ/TD/CP/AM 151008

### **Mini-Circuits**

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

## **Performance Charts**

at IF Freq of 30 MHz

7.5

4.5 0.1

70

60

50

40

30


20


0


Notes

**ISOLATION (dB)** 

VSWR







TUF-3+

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit shandard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

### Mini-Circuits