

Non-Catalog Model

Frequency Mixer

TUF-3H

Level 17 (LO Power +17 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request.
Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : B02

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	0.15		400	MHz
	RF (fL to fU)	0.15		400	MHz
	IF	0		400	MHz
Conversion Loss	mid band		5.0	7.0	dB
	Total Range			8.0	dB
LO-RF Isolation	Low Range	50	60		dB
	Mid Range	35	50		dB
	Upper Range	30	40		dB
LO-IF Isolation	Low Range	40	60		dB
	Mid Range	25	45		dB
	Upper Range	20	35		dB
IP3 Input		+27.5	+30		dBm
1 dB Comp. Input Power			+14		dBm

Notes: Low Range = [fL to 10fL] Mid Range = [10fL to fU/2] Upper Range = [fU/2 to fU]
mid band = [2fL to fU/2]

IP3 : RF Power = 0 dBm @ 200 MHz & 202 MHz , LO Power = +17 dBm @ 180 MHz
Non-hermetic

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA

PIN CONNECTIONS	
LO	4
RF	1
IF	2
GROUND	3

Electrical Schematics

