

Frequency Mixer

TUF-ED12915/1

Level 10 (LO Power + 10 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : NNN150

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fu)	5		600	MHz
	RF (fL to fu)	5		600	MHz
	IF	.25		600	MHz
Conversion Loss	mid band		6.08		dB
	Total Range		6.15		dB
LO-RF Isolation	Low Range		51		dB
	Mid Range		42		dB
	Upper Range		32		dB
LO-IF Isolation	Low Range		49		dB
	Mid Range		42		dB
	Upper Range		33		dB
Input IP3			+18		dBm
1 dB Compression			+5		dBm

Note: Low Range = [fL to 10fL]
mid band = [2fL to fu/2]

Mid Range = [10fL to fu/2]

Upper Range = [fu/2 to fu]

MAXIMUM RATINGS	
Operating Temperature	-55°C TO +100°C
Storage Temperature	-55°C TO +100°C

PIN CONNECTIONS	
LO	4
RF	1
IF	2
GROUND	3
CASE GROUND	3

Electrical Schematics

