

Frequency Mixer

TUF-ED12916/4

Level 7 (LO Power + 7 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



CASE STYLE : NNN150

Please click "Back", and then click "Contact Us" for Applications support.

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fu)	20		1500	MHz
	RF (fL to fu)	20		1500	MHz
	IF	10		1200	MHz
Conversion Loss	mid band		5.9		dB
	Total Range		6.5		dB
LO-RF Isolation	Low Range		55		dB
	Mid Range		46		dB
	Upper Range		43		dB
LO-IF Isolation	Low Range		38		dB
	Mid Range		28		dB
	Upper Range		22		dB
Input IP3			+12		dBm
1 dB Compression			+1		dBm

Note: Low Range = [fL to 10fL]
mid band = [2fL to fu/2]

Mid Range = [10fL to fu/2]

Upper Range = [fu/2 to fu]

MAXIMUM RATINGS	
Operating Temperature	-55°C TO +100°C
Storage Temperature	-55°C TO +100°C

PIN CONNECTIONS	
LO	4
RF	1
IF	2
GROUND	3
CASE GROUND	3

Electrical Schematics

