# Surface Mount RF Transformer

0.8 to 500 MHz  $50\Omega$ 


# **Maximum Ratings**

Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25W
DC Current	30mA
Democrat democrat de marche de march	of the condition the condition of the condition

## **Pin Connections**


PRIMARY DOT	4
PRIMARY	6
SECONDARY DOT	3
SECONDARY	1
NOT USED	2,5

# **Outline Drawing**



## Outline Dimensions (inch)

F	<b>E</b>	<b>D</b>	<b>C</b>	<b>B</b>	<b>A</b>
. <b>055</b>	. <b>050</b>	. <b>100</b>	. <b>20</b>	. <b>31</b>	. <b>250</b>
1.40	1.27	2.54	5.08	7.87	6.35
wt		<b>K</b>	J	H	G
grams		. <b>050</b>	. <b>270</b>	. <b>070</b>	.040
0.50		1.27	6.86	1.78	1.02



# **Features**

- wideband, 0.8 to 500 MHz
- excellent return loss

# **Applications**

- VHF/UHF
- receivers/transmitters

# TX1-R5+ **TX1-R5**



Generic photo used for illustration numoses only CASE STYLE: TT240

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


# **Transformer Electrical Specifications**

Ω	FREQUENCY	3 dB	INSERTION LOSS*  2 dB MHz	1 dB
RATIO	(MHz)	MHz		MHz
1	0.8-500	0.8-500	1.2-350	3.2-180

<sup>\*</sup> Insertion Loss is referenced to mid-band loss, 0.7 dB typ

# **Typical Performance Data**

FREQUE (MHz			3
0.80	0.87	11.84	
1.20	0.87	13.26	
2.20	0.87	15.37	
3.20	0.86	16.68	
91.60	0.74	14.38	
180.00	0.92	10.21	
265.00	1.32	7.79	
350.00	1.28	6.22	
425.00	1.87	5.32	
500.00	2.01	4.63	



A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp