

Non-Catalog Model

RF Transformer

TX16-1

Impedance Ratio : 16

Important Note

This is a non-catalog model and can be manufactured on specific request.
Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : TT240

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	0.4		120	MHz
Insertion Loss *	3 dB Bandwidth	0.4 - 120		MHz
	2 dB Bandwidth	0.7 - 80		MHz
	1 dB Bandwidth	5 - 20		MHz

Notes:

* Insertion Loss is referenced to mid-band loss, 0.67dB typ.
Non-hermetic

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25 W
DC Current	30 mA

PIN CONNECTIONS	
PRIMARY DOT	4
PRIMARY	6
SECONDARY DOT	3
SECONDARY	1
NOT USED	2,5

Configuration : C

