# **Wideband Gain Amplifier**

YSF-322+

# The Big Deal:

- Excellent Combination of gain, P1dB, IP3 and NF
- Flat Gain Response:
  - ± 2.2 dB over 900-3200 MHz
- 50Ω Input and Output: no External Components Required





# **Product Overview:**

YSF-322+ is an advanced amplifier module in a Mini-Circuits System In Package MSIP. This module is fully matched to  $50\Omega$  in/out impedance and has built-in Input & Output DC block capacitors. It is enclosed in a 5 x 6 mm MCLP plastic package. The YSF-322+ uses E-PHEMT technology enabling it to work with a single positive supply voltage.

# **Key Features**

Feature	Advantages
Strong Combination of Performance	The YSF-322+ provides a strong combination of performance parameters including high gain (20 dB), high IP3 (+35 dBm) and P1dB (+20 dBm) and low noise figures (2.8 dB) that are difficult to achieve in a single stage design and available only in the YSF amplifier series.
Broadband Gain Flatness ± 2.2dB	The YSF-322+ provides outstanding gain flatness over a broad frequency range covering 900 to 3200 MHz making this ideal for use in applications where gain-flatness and repeatability are critical performance requirements.
High Gain	The YSF-322+ is a two-stage design with internal feedback and bias to provide flat 20 dB nominal gain, supporting applications where a single gain block must overcome large system losses such as long cable runs and lossy components.
Integrated Matching, DC Blocking and Bias in Small Package	The YSF-322+ includes all support circuits including: Matching, Bias and DC Blocking, all integrated into a single 5x6mm package making the total footprint equal to or smaller than most solutions.
Excellent Return Loss	The YSF-322+ includes integrated input and output matching and bias circuits to make this amplifier a simple, complete drop-in solution. The matching circuits provide excellent output return loss (20dB), and are designed to give optimal P1dB and IP3 performance in a $50\Omega$ environment.
High Reverse Isolation	With 30 dB of reverse isolation – the YSF-322+ is an ideal gain block for use in integrated systems to minimize VSWR interactions resulting from cascading highly reflective components such as sharp filters.

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuit satandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



# **Wideband Amplifier**

0.9-3.2 GHz

### **Product Features**

- Matched 50-ohm surface mount amplifier
- High gain, 20 dB typ. at 2 GHz
- Up to +20 dBm typ. output power at 2 GHz
- High IP3, +35 dBm at 2 GHz
- Low Noise Figure, 2.8 dB typ. at 2 GHz
- High directivity, 30 dB isolation
- Internal Input & Output DC Block
- Separate terminal for DC
- Protected by us patent 8,994,157

# **Typical Applications**

- Cellular
- Portable Wireless
- Receivers & transmitters
- Radar
- GSM
- WiMax
- Instrumentation

CASE STYLE: DL1636

### +RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




# **General Description**

YSF-322+ is an advanced amplifier module in a Mini-Circuits System In Package MSIP. This module is fully matched to  $50\Omega$  in/out impedance and has built-in Input & Output DC block capacitors. It is enclosed in a 5 x 6 mm MCLP plastic package. The YSF-322+ uses E-PHEMT\* technology enabling it to work with a single positive supply voltage.

# simplified schematic and pad description





Function	Pad Number	Description
RF-IN	5	RF Input
RF-OUT	3	RF Output
DC	4	DC Supply
GND	Paddle	Connected to ground
NOT USED	1,2,6,7,8	No internal connection

<sup>\*</sup>Enhancement mode Pseudomorphic High Electron Mobility Transistor

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp





# Electrical Specifications<sup>(1)</sup> at 25°C, Zo=50Ω unless noted

Parameter	Condition (MHz)	Min.	Тур.	Max.	Units
Frequency Range		900		3200	MHz
	900	18.6	20.4	22.4	dB
O-i-	1700	17.8	19.8	22.0	
Gain	2500	17.1	19.0	21.5	
	3200	14.4	16.0	18.6	
Gain Flatness			± 2.2		dB
	900	_	10.0		
118.	1700	_	10.0		
Input Return Loss	2500	10.0	15.0		dB
	3200	_	21.0		
	900	_	14.0		
0.1.18.1	1700	_	23.5		dB
Output Return Loss	2500	12.0	17.0		
	3200	_	10.4		
Reverse Isolation			30.0		dB
	900	_	20.0		dBm
0.4.15	1700	_	20.0		
Output Power @1 dB compression	2500	18.0	20.0		
	3200	_	20.0		
Output Power @3 dB compression			21.0		dBm
	900	_	36.0		dBm
0	1700	30.0	35.0		
Output IP3	2500	_	35.0		
	3200	_	35.0		
	900		3.5	_	
	1700		3.0	4.0	dB
Noise Figure	2500		2.5	_	
	3200		2.5	_	
Device Operating Voltage			5		V
Device Operating Current			118	145	mA
Device Current Variation vs. Temperature <sup>(2)</sup>			2		μΑ/°C
Device Current Variation vs Voltage			0.002		mA/mV
Thermal Resistance, junction-to-ground lead <sup>(3)</sup>			56		°C/W

<sup>(1)</sup> Measured on Mini-Circuits Characterization test board TB-616+. See Characterization Test Circuit (Fig. 1)


# **Absolute Maximum Ratings**

Parameter	Ratings	Units	
Operating Temperature <sup>(4)</sup>	-40 to 85	°C	
Storage Temperature	-65 to 150	°C	
DC Voltage on Pad 4	7	V	
Power Dissipation	1.5	W	
Input Power	21	dBm	

Note: Permanent damage may occur if any of these limits are exceeded.

These ratings are not intended for continuous normal operation.

(4) Case is defined as ground paddle.



<sup>(2)</sup> D(+85°C to -45°C)

<sup>(3)</sup> Thermal Resistance= Hot spot temperature - Ground lead temperature

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuit satandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

## **Characterization Test Circuit**




Fig 1. Block Diagram of Test Circuit used for characterization. (DUT soldered on Mini-Circuits Characterization Test Fixture TB-616+) Gain, Return loss, Output power at 1dB compression (P1 dB), Output IP3 (OIP3) and Noise Figure measured using Agilent's N5242A PNA-X microwave network analyzer.

## Conditions:

- 1. Gain: Pin= -25dBm
- 2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.

# **Recommended Application Circuit**

(refer to evaluation board for PCB Layout and component values)





Fig 2. Recommended Application Circuit

## **Product Marking**



A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuit standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Additional Detailed Technical Information additional information is available on our dash board. To access this information click here				
	Data Table			
Performance Data	Swept Graphs			
	S-Parameter (S2P Files) Data Set (.zip file)			
Case Style	DL1636 Plastic package, exposed paddle, lead finish: tin/silver/nickel			
Tape & Reel	F68			
Standard quantities available on reel	7" reels with 20, 50, 100, 200, 500 or 1K devices. 13" reels with 2K, or 4K devices.			
Suggested Layout for PCB Design	PL-352			
Evaluation Board	TB-616-1+			
Environmental Ratings	ENV08T1			

# **ESD Rating**

Human Body Model (HBM): Class 1A in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (25V) in accordance with ANSI/ESD STM5.2-1999




**Attention** Observe precautions for handling electrostatic sensitive devices

## **MSL Rating**

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D

### **MSL Test Flow Chart**



A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuit satandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp