

50Ω DC to 216 MHz

## **ULP-216+**

## **The Big Deal**

- Low Insertion loss, 1.5dB Typ.
- High rejection, > 40dB
- Sharp insertion loss roll-off
- Ultra miniature surface mount package



CASE STYLE: QA2224

## **Product Overview**

The ULP-216+ is a lowpass filter in a top hat package (size of 0.25" x 0.25") fabricated using SMT technology. Covering DC to 216 MHz band width, these units offer good matching within the passband and high rejection. This model uses a miniature high Q capacitors and chip inductors for high reliability. In addition it has repeatable performance across production lots and consistent performance across temperature.

## **Key Features**

Feature	Advantages
Low passband insertion loss	Passband insertion loss 1.5dB typical ensures low signal loss throughout the passband
Excellent stopband rejection	Rejection of 40 dB ensures unwanted spurious are eliminated
Excellent return loss at DC-216 MHz	This makes signal transmission with very less reflections and well-matched with the adjacent com- ponent used in the system
Small size, 0.25" x 0.25"	The Ultra miniature surface mount package enables the ULP-216+ to be used in compact designs.

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

# Surface Mount **Low Pass Filter**

50Ω DC to 216 MHz

## ULP-216+



CASE STYLE: QA2224

Тур.

1.5

3.0

1.3

27

47

20

Max.

2.0

\_

Unit

dB

dB

:1

dB

dB

:1

Min.

\_

20

40


#### **Features**

- · High rejection
- · Sharp insertion loss roll-off
- · Ultra miniature surface mount package


#### **Applications**

- Wireless communications
- Receivers / Transformers
- Lab use

#### **Functional Schematic**



### **Typical Frequency Response**



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings			
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		
RF Power Input	1 W max.		

Permanent damage may occur if any of these limits are exceeded.

Parameter

Pass Band

Stop Band

Insertion Loss

Freq. Cut-Off

**Rejection Loss** 

**Rejection Loss** 

VSWR

VSWR

#### Typical Performance Data at 25°C

Electrical Specifications at 25°C

Frequency (MHz)

DC-216

232

DC-216

295-450

450-1300

295-1300

F#

DC-F1

F2


DC-F1


F3-F4


F4-F5

F3-F5

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	0.16	1.03	1	3.33
10	0.17	1.03	3	3.11
50	0.29	1.04	5	3.04
100	0.47	1.14	10	3.02
200	1.09	1.24	50	3.05
216	1.40	1.04	60	3.09
232	3.38	2.46	70	3.14
250	11.36	9.23	80	3.19
260	16.91	13.91	90	3.26
267	20.84	16.61	100	3.34
283	30.21	21.17	110	3.42
295	38.52	23.77	120	3.53
340	45.35	31.96	130	3.67
450	49.18	52.29	140	3.84
500	51.25	62.43	150	4.06
750	54.40	127.26	160	4.32
1000	54.99	199.91	180	4.99
1100	54.71	228.39	200	6.07
1200	53.94	242.75	210	7.18
1300	52.26	253.18	216	8.20







4

2

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

## ∭Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.A M161927 ULP-216+ EDU2391 URJ 170513 Page 2 of 3


216




#### **Pad Connections**

INPUT	1
OUTPUT	3
GROUND	2,4,5,6

Demo Board MCL P/N: TB-894+ Suggested PCB Layout (PL-484)





#### NOTES:


TRACE WIDTH IS SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .020°±.0015". COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC

(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK



K
-
.046
1.17
Wt.
grams
0
0.25

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Min-Circuits and ard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

## **Mini-Circuits**