

50Ω DC to 320 MHz

## **ULP-320+**

## **The Big Deal**

- Low Insertion loss, 1.5dB Typ.
- High rejection, > 40dB
- Sharp insertion loss roll-off
- Ultra miniature surface mount package



CASE STYLE: QA2224

### **Product Overview**

The ULP-320+ is a lowpass filter in a top hat package (size of 0.25" x 0.25") fabricated using SMT technology. Covering DC to 320 MHz band width, these units offer good matching within the passband and high rejection. This model uses a miniature high Q capacitors and chip inductors for high reliability. In addition it has repeatable performance across production lots and consistent performance across temperature.

## **Key Features**

Feature	Advantages
Low passband insertion loss	Passband insertion loss 1.5dB typical ensures low signal loss throughout the passband
Excellent stopband rejection	Rejection of 40 dB ensures unwanted spurious are eliminated
Excellent return loss at DC-320 MHz	This makes signal transmission with very less reflections and well-matched with the adjacent com- ponent used in the system
Small size, 0.25" x 0.25"	The Ultra miniature surface mount package enables the ULP-320+ to be used in compact designs.

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



# Surface Mount **Low Pass Filter**

50Ω DC to 320 MHz

# ULP-320+



CASE STYLE: QA2224

**T**....


140

#### **Features**


- · High rejection
- · Sharp insertion loss roll-off
- · Ultra miniature surface mount package

#### **Applications**

- Wireless communications
- Receivers / Transformers
- Lab use



#### **Typical Frequency Response**



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical	Specifications	at 25°C	,
F#	Frequency (MHz)	Min	

FC	arameter	Г#	Frequency (wriz)	IVIIII.	тур.	wax.	Unit
	Insertion Loss	DC-F1	DC-320	_	1.5	2.0	dB
Pass Band	Freq. Cut-Off	F2	345	_	3.0	—	dB
	VSWR	DC-F1	DC-320	_	1.4	—	:1
Stop Band	Rejection Loss	F3-F4	440-700	20	27	—	dB
	Rejection Loss	F4-F5	700-1600	40	47	—	dB
	VSWR	F3-F5	440-1600	_	20	—	:1

Maximum Ratings						
Operating Temperature	-40°C to 85°C					
Storage Temperature	-55°C to 100°C					
RF Power Input	1.6 W max.					

Deve

Permanent damage may occur if any of these limits are exceeded.


#### Typical Performance Data at 25°C


Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)	
1	0.11	1.02	1	2.42	
10	0.13	1.03	2	2.25	
100	0.31	1.04	5	2.10	
150	0.43	1.13	10	2.09	
320	1.26	1.17	50	2.08	
345	2.92	2.14	80	2.12	
346	3.10	2.27	100	2.16	
375	12.67	10.73	120	2.19	
395	20.88	17.81	140	2.28	
416	30.08	23.24	160	2.35	
440	44.90	28.17	180	2.45	
450	55.27	29.97	200	2.57	
475	44.06	34.32	210	2.65	
510	41.61	40.34	230	2.86	
600	43.55	55.67	250	3.14	
700	46.26	73.86	270	3.49	
1000	49.86	135.66	300	4.23	
1250	50.81	184.02	310	4.69	
1500	49.99	220.58	318	5.23	
1600	48.82	227.43	320	5.40	


INSERTION LOSS (dB)

(su)

**GROUP DELAY** 







A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's trandard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

## ∭Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.A M161927 ULP-320+ EDU2395 URJ 170513 Page 2 of 3




#### **Pad Connections**

INPUT	1
OUTPUT	3
GROUND	2,4,5,6


Demo Board MCL P/N: TB-894+ Suggested PCB Layout (PL-484)






#### NOTES:

TRACE WIDTH IS SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .020°±.0015". COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK



Α	В		С	D	E	F	G	н	J	K
-	-	Min	Max	-	-	-	-	-	-	-
.250	.250	.075	.100	.075	.125	.092	.201	.041	.050	.046
6.35	6.35	1.91	2.54	1.91	3.18	2.34	5.11	1.04	1.27	1.17
L	M		N	Р	Q					Wt.
-	-		-	-	-					grams
.168	.117		.042	.260	.234					0.25
4.27	2.97		1.07	6.60	5.94					0.25

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Min-Circuits and ard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

## **Mini-Circuits**