

50Ω DC to 83 MHz

The Big Deal


- Low Insertion loss, 1.5dB Typ.
- High rejection, > 40dB
- Sharp insertion loss roll-off
- Good VSWR
- · Ultra miniature surface mount package

Product Overview

The ULP-83+ is a lowpass filter in a top hat package (size of 0.25" x 0.25") fabricated using SMT technology. Covering DC to 83 MHz band width, these units offer good matching within the passband and high rejection. This model uses a miniature high Q capacitors and chip inductors for high reliability. In addition it has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages	
Low passband insertion loss	Passband insertion loss 1.5dB typical ensures low signal loss throughout the passband	
Excellent stopband rejection	Rejection of 40 dB ensures unwanted spurious are eliminated	
Excellent return loss at DC-83 MHz	This makes signal transmission with very less reflections and well-matched with the adjacent com- ponent used in the system	
Small size, 0.25" x 0.25"	The Ultra miniature surface mount package enables the ULP-83+ to be used in compact designs.	



ULP-83+

CASE STYLE: QA2224

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Surface Mount **Low Pass Filter**

50Ω DC to 83 MHz



CASE STYLE: QA2224

Тур.

1.5

3.0

1.1

27

47

20

Max.

2.0

_

Unit

dB

dB

:1

dB

dB

:1

Min.

_

20

40


_

Features


- · High rejection
- · Sharp insertion loss roll-off
- · Good VSWR, 1.1:1 typ. at passband
- · Ultra miniature surface mount package

Applications

- Wireless communications
- Receivers / Transformers
- Lab use



Typical Frequency Response





VSWR F3-F5 135-850 Maximum Rating

F#

DC-F1

F2

DC-F1

F3-F4

F4-F5

Maximum Hatingo				
Operating Temperature	-40°C to 85°C			
Storage Temperature	-55°C to 100°C			
RF Power Input	0.15W max.			

Parameter

Pass Band

Stop Band

Insertion Loss

Freq. Cut-Off

Rejection Loss

VSWR

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Electrical Specifications at 25°C

Frequency (MHz)

DC-83


93


DC-83


118-135

135-850

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	0.49	1.10	1	7.38
10	0.49	1.12	2	7.32
40	0.65	1.03	5	7.36
80	1.33	1.05	10	7.32
83	1.46	1.05	15	7.38
90	2.12	1.29	20	7.49
93	2.91	1.75	25	7.49
94	3.32	1.99	35	7.97
100	7.99	4.88	40	8.07
105	13.83	8.64	45	8.46
110	20.05	11.98	50	8.72
118	30.11	15.84	55	9.12
130	47.92	20.24	60	9.67
135	60.20	21.89	65	10.32
200	72.50	42.77	68	10.72
400	73.75	126.88	70	11.17
500	72.57	173.05	75	12.27
600	73.45	234.35	78	13.18
700	73.60	289.59	80	13.82
850	69.00	355.59	83	15.20







A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's trandard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

∭Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

340 510 FREQUENCY (MHz)

REV OR M156166 ULP-83+ EDU2384 URJ 170511 Page 2 of 3


Low Pass Filter




Pad Connections

INPUT	1
OUTPUT	3
GROUND	2,4,5,6

Demo Board MCL P/N: TB-894+ Suggested PCB Layout (PL-484)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK



A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectived), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits