Coaxial **High Power Combiner**

ZA2CS-251-20W+

2 Way-0° 50Ω 10 to 250 MHz 20 Watt

The Big Deal

- High power, up to 20W as a combiner (each input port)
- Low insertion loss, 0.17 dB
- High isolation, 25 dB
- Low unbalance, 0.5°/0.05 dB



CASE STYLE: AW254

Product Overview

Mini-Circuits' ZA2CS-251-20W+ is a 2-way 0° splitter/combiner providing 20W power handling and very low insertion loss across the 10 to 250 MHz band, covering applications including AM/FM radio, VHF/UHF, instrumentation and more. Its low intrinsic losses provide excellent signal fidelity from input to output, even to high-power signals. This model also provides high isolation and very low amplitude and phase unbalance. It features rugged construction with your choice of SMA or N-Type connectors and a heat sink for efficient cooling.

Key Features

Feature	Advantages
Feature 1 High power handling: • Up to 25W as a splitter • Up to 20W as a combiner	Suitable for many high power applications.
Very low insertion loss, 0.17 dB	Very low insertion loss minimizes intrinsic losses, making this model a suitable candidate for high power signal distribution applications where low loss is a requirement.
Very low unbalance: • 0.05 dB amplitude unbalance • 0.5° phase unbalance	ZA2CS-251-20+ produces nearly equal output signals, ideal for parallel path / multichannel systems.
Good isolation, 25 dB	Minimizes interference between input ports.
Excellent VSWR, 1.1:1 typ.	Provides excellent thru-path transmission with low signal reflection.

- A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collective), "Standard Terms"), Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Notes

Coaxial **High Power Combiner**

2 Wav-0° 50Ω 10 to 250 MHz 20 Watt

Maximum Ratings

Operating Temperature	-55°C to 60°C
Storage Temperature	-55°C to 100°C
Permanent damage may occur if any	of these limits are exceeded.

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2

Outline Drawing



Outline Dimensions (inch)

B 2.06	C 1 92	D 100	E 2 500	F 1 525
52.32	48.77	2.54	63.50	38.74
Н	J	К		wt
H 1.000	J .50	K 2.00		wt grams
	B 2.06 52.32	BC2.061.9252.3248.77	B C D 2.06 1.92 .100 52.32 48.77 2.54	B C D E 2.06 1.92 .100 2.500 52.32 48.77 2.54 63.50

Electrical Schematic





Features

- high power, up to 20W input power as combiner
- low insertion loss, .17 dB typ.
- high isolation, 30 dB typ.
- excellent VSWR, 1.1:1 typ.

Applications

- instrumentation
- VHF/UHF
- AM/FM RADIO

ZA2CS-251-20W+



Generic photo used for illustration purposes only CASE STYLE: AW254

Connectors Model N-TYPE

SMA

ZA2CS-251-20WN+ ZA2CS-251-20WS+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Para	ameter	Frequency (MHz)	Min.	Тур.	Max.	Unit		
Frequency Range			10		250	MHz		
Insertion Loss Abov	ve 3.0 dB	10 - 250 25 - 120	_	0.25 0.17	0.5 0.4	dB		
Isolation		10 - 250 25 - 120	15 20	20 25	_	dB		
Phase Unbalance		10 - 250	_	0.5	2 Degree			
Amplitude Unbaland	ce	10 - 250	_	.05	0.25 dB			
VSWR (Port S)		10 - 250	_	1.15	1.5 :1			
VSWR (Port 1-2)		10 - 250	_	1.20	1.6 :1			
Power Input	as combiner*	10 - 250	-	-	10			
		25 - 120	_	—	20			
	ee enlitter	10 - 250	-	—	25	vv		
	as spinter	25 - 120	_	_	65			

* Maximum Power Input for each port.

Typical Performance Data

Frequency (MHz)	Total (d	Loss¹ B)	Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
10	3.06	3.05	0.01	24.19	0.01	1.16	1.27	1.27
25	3.14	3.12	0.02	30.88	0.01	1.11	1.11	1.11
35	3.15	3.13	0.02	32.38	0.02	1.11	1.09	1.09
45	3.16	3.14	0.02	32.61	0.02	1.11	1.09	1.09
50	3.16	3.14	0.02	32.30	0.03	1.11	1.09	1.09
60	3.16	3.15	0.02	31.28	0.02	1.11	1.08	1.08
65	3.17	3.15	0.02	30.68	0.02	1.11	1.08	1.08
75	3.17	3.15	0.01	29.51	0.03	1.11	1.08	1.08
85	3.17	3.16	0.01	28.43	0.03	1.11	1.08	1.08
90	3.17	3.16	0.01	27.93	0.03	1.11	1.08	1.08
120	3.18	3.17	0.01	25.60	0.05	1.12	1.08	1.08
150	3.18	3.18	0.01	23.82	0.06	1.12	1.08	1.08
180	3.18	3.19	0.00	21.82	0.08	1.13	1.08	1.08
210	3.20	3.21	0.01	20.31	0.12	1.15	1.09	1.08
250	3.24	3.25	0.02	19.47	0.16	1.17	1.10	1.09

1. Total Loss = Insertion Loss + 3dB splitter theoretical loss



VSWR 1.3 VSWR S ---VSWR 2 VSWR 1.25 1.2 ⊔2 1.2 MS 1.15 1.1 -----1.05 10 58 106 154 202 250 FREQUENCY (MHz)

ZA2CS-251-20W+

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

REV. B M156482 ZA2CS-251-20W+ ED-17141 JX/CP/AM 200512 Page 2 of 2

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com