# **N-Type Fixed Attenuator**

**1W** 15dB DC to 6000 MHz  $50\Omega$ 

### **Maximum Ratings**

Operating Temperature -45°C to 100°C Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded

#### **Features**

- wideband coverage, DC to 6000 MHz
- 1 watt rating
- rugged unibody construction
- · off-the-shelf availability
- · very low cost

#### **Applications**

- impedance matching
- · signal level adjustment

## **UNAT-15+**




Connectors Model N-Type UNAT-15+

#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### **Outline Drawing**



# Outline Dimensions (inch )

wt	Е	D	В
grams	.718	2.11	.68
72.5	18.24	53.59	17.27


#### **Electrical Specifications**


FREQ. RANGE (MHz)	ATTENUATION * (dB) Flatness **				VSWR (:1)		MAX. INPUT POWER		
		DC-3 GHz	3-4.5 GHz	4.5-6 GHz	DC-6 GHz	DC-3 GHz	3-4.5 GHz	4.5-6 GHz	(W)
	Nom.	Тур.	Тур.	Тур.	Тур.	Тур. Мах.	Тур. Мах.	Тур.	
DC-6000	15±0.3	0.20	0.35	0.20	0.60	1.15 1.43	1.20 1.80	1.70	1.0

<sup>\*</sup> Attenuation varies by 0.3 dB max. over temperature.

#### **Typical Performance Data**

Frequency (MHz)	Attenuation (dB)	VSWR (:1)	
10	14.97	1.00	
50	15.01	1.00	
100	15.01	1.00	
500	15.06	1.02	
1000	15.08	1.05	
1600	15.17	1.09	
2000	15.22	1.13	
2500	15.28	1.18	
3000	15.46	1.23	
3500	15.54	1.28	
4000	15.65	1.33	
4500	15.80	1.41	
5000	15.91	1.49	
5500	16.11	1.60	
6000	16.44	1.74	





A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement ins.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively: "Standard Terms"): Purchases of this part. Ferrormance and updany attributes and contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

<sup>\*\*</sup> Flatness= variation over band divided by 2.