DC to 10 MHz Pass **Bi-Directional Coupler**

ZABDC20-232H+

50Ω Up to 50W 800 to 2300 MHz

The Big Deal

- Excellent mainline loss, 0.25 dB typ.
- Excellent directivity, 23 dB typ.
- DC pass through, 2.0 A max @ 50 W RF power
- 10 MHz pass through



CASE STYLE: DD477-1

Product Overview

Mini-Circuits ZABDC20-232H+ is a 20-dB bi-directional coupler ideal for power leveling and monitoring L-band applications. The rugged aluminum alloy case measures 2.0" x 2.0" x 0.88" high, with gold-plated SMA or N-type connectors.

Kev Features

Feature	Advantages				
Mainline loss 0.25 dB typ.	Extremely low mainline loss for applications where signal strength is key, such as GPS, CDMA, UMTS, and LTE base station transmitters				
Directivity 23 dB typ.	Enables more accurate sampling for VSWR measurements				
DC pass through 2.0 A max.	Allows flexible deployment between active components and their DC power supplies				
10 MHz pass through	Pass through at 10 MHz supports reference clock frequency communication to remote systems				
Full L band coverage	Extended frequency range makes this coupler ideal for use in satcom systems, such as LNB/ BUC installations				

- A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Notes

DC to 10 MHz Pass **Bi-Directional Coupler**

Up to 50W 800 to 2300 MHz 50Ω

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
DC Current	2.0 A

* Case temperature is defined as temperature on ground leads. Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

INPUT	1
OUTPUT	4
COUPLED (forward)	2
COUPLED (reverse)	3

Features

- excellent mainline loss, 0.25 dB typ.
- excellent directivity, 23 dB typ. • high power, up to 50W
- rugged shielded case
- DC current through input to output 2.0A Max. at 50 watt RF input power
- 10 MHz pass through

Applications

- L Band
- PCS/DCS/UMTS
- power leveling & monitoring VSWR measurement
- satellite communication

ZABDC20-232H+



Generic photo used for illustration purposes only

CASE STYLE: DD477-1


Connectors Model SMA N-Type

ZABDC20-232H+ ZABDC20-232H-N+

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Тур.	Max.	Units	
Frequency Range		800		2300	MHz	
	800-2300	—	0.23	0.35		
Mainline Loss	950-1250	_	0.17	0.30	dB	
(above theoretical 0.05 dB)	1700-2050	_	0.21	0.35	uБ	
	950-2150	_	0.22	0.35		
	800-2300	—	20.5±1.5	—		
Coupling	950-1250	_	20.5±1.0	_	dB	
Coupling	1700-2050	_	19.5±0.8	_	ub	
	950-2150	_	20.5±1.2	—		
	800-2300	—	1.5	1.9		
Coupling Flatness (±)	950-1250	_	0.7	0.9	dB	
Coupling Flattless (±)	1700-2050	-	0.5	0.7	uв	
	950-2150	_	1.0	1.3		
	800-2300	17	20	_		
Directivity	950-1250	18	20	_	dB	
Directivity	1700-2050	19	23	—		
	950-2150	18	20			
	800-2300	18	23	_		
Return Loss (Input)	950-1250	18	23	—	dB	
netum 2035 (input)	1700-2050	20	24	-	uр	
	950-2150	18	23			
	800-2300	18	23	—		
Return Loss (Output)	950-1250	18	23	—	dB	
	1700-2050	20	25	—	uD	
	950-2150	18	23			
Return Loss (Coupling)	800-2300	16	19	—		
	950-1250	17	19	—	dB	
notarii 2000 (Ocapinig)	1700-2050	16	20	—	20	
	950-2150	16	19	—		
Input Power	800-2300	_	_	50	W	




Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A M151107 ED-14207/1 ZABDC20-232H+ WP/CP/AM 200505 Page 2 of 3



Outline Drawing


Outline Dimensions	$\binom{inch}{mm}$
---------------------------	--------------------


A	B	C	D	E	F	G
2.00	2.00	.88	.90	.156	1.688	. 125
50.80	50.80	22.35	22.86	3.96	42.88	3.18
H . 38 9.65	J 	К . 50 12.70	L 1.00 25.40	M 1.25 31.75		wt grams 225


ZABDC20-232H+

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)		Directivity (dB)		Return Loss (dB)			
	In-Out	In-Cpl Fwd	Out-Cpl Rev	Out-Cpl Fwd	In-Cpl Rev	In	Out	Cpl Fwd	Cpl Rev
800.00	0.14	22.19	22.18	20.87	20.60	25.12	25.06	22.48	22.54
950.00	0.16	21.10	21.09	21.04	20.91	24.16	24.04	21.21	21.44
1100.00	0.19	20.29	20.27	21.70	21.72	23.65	23.62	20.37	20.62
1250.00	0.20	19.67	19.66	22.84	23.00	23.74	23.78	19.94	20.17
1500.00	0.22	19.08	19.09	24.24	24.44	24.98	24.97	20.11	20.35
1700.00	0.23	18.98	18.97	24.82	24.88	27.55	27.56	21.72	21.83
1950.00	0.23	19.27	19.27	24.65	24.03	37.97	37.62	26.69	26.61
2050.00	0.23	19.54	19.53	24.19	23.74	49.29	39.04	30.82	30.31
2150.00	0.23	19.92	19.90	24.15	23.44	34.53	33.03	37.03	35.01
2300.00	0.24	20.69	20.68	23.47	22.50	27.11	26.92	30.45	29.88

Typical Performance Data







Notes

Notes A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collective), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

