Bandpass Filter

ZABP-550-S+

 50Ω 100 to 1000 MHz



Generic photo used for illustration purposes only CASE STYLE: UU1842

The Big Deal

- · High rejection
- Good VSWR
- Connectorized package

Product Overview

ZABP-550-S+ is a 50Ω bandpass filter with a rugged connectorized package covering the passband of 100 to 1000 MHz. The bandpass filter offers good matching within the passband and provides high rejection. This filter has miniature high Q capacitors and wire welded inductors for high reliability. It has repeatable performance across lots and consistent performance across temperature.

Key Features

Feature	Advantages		
High rejection	ZABP-550-S+ has sharper transition and rejects spurious signals in the stopband.		
Good VSWR	This filter maintains typical VSWR over passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple.		
Connectorized package	Connectorized package is easy to interface with other devices and well suited for test setups.		

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warrantly and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

· Sharp roll-off

Good VSWR

Applications

Cellular network

Test equipment

Ultra wide bandwidth

· Connectorized package

· Receiver front end applications

· Civil aircraft communication radio

Bandpass Filter

 50Ω 100 to 1000 MHz

ZABP-550-S+



Generic photo used for illustration purposes only

CASE STYLE: UU1842 Connectors Model

ZABP-550-S+ SMA-M\F


Electrical Specifications at 25°C

Electrical Specifications at 25 C							
Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	-	-	-	550	-	MHz
Pass Band	Insertion Loss	F1-F2	100-1000	-	1.1	2.2	dB
	VSWR	F1-F2	100-1000	-	1.5	2.1	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 80	40	50	-	dB
	VSWR	DC-F3	DC - 80	-	20	-	:1
Stop Band, Upper	Insertion Loss	F4-F5	1200-2000	30	40	-	dB
	VSWR	F4-F5	1200-2000	-	20	-	:1


Maximum Ratings			
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		
RF Power Input	1 W max.		

Permanent damage may occur if any of these limits are exceeded.

Functional Schematic




Typical Frequency Response





+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1	99.59	46461.03	100	31.04
25	69.03	2049.79	125	9.40
50	67.70	281.03	150	4.99
80	51.48	26.64	200	3.65
83	48.25	18.10	250	2.55
85	32.84	13.50	300	2.05
88	20.37	8.96	350	1.79
90	11.15	5.66	400	1.64
94	3.48	2.54	450	1.54
100	1.23	1.24	500	1.49
550	0.47	1.33	550	1.47
1000	0.95	1.16	600	1.48
1090	3.70	2.11	650	1.50
1110	9.66	5.46	700	1.55
1125	16.25	8.77	750	1.60
1133	20.18	10.25	800	1.69
1151	30.32	12.61	850	1.82
1200	50.19	16.16	900	2.02
1600	52.37	20.19	950	2.25
2000	42.64	21.45	1000	2.95









Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Coaxial Connections

PORT - 1	SMA-MALE
PORT - 2	SMA-FEMALE

Outline Drawing





Outline Dimensions (inch mm)

Е	D	С	В	Α
2.125	2.175	.750	2.250	2.300
53.98	55.25	19.05	57.15	58.42
		н	G	-
				•
grams	1.125	.312	.125	.125
124	28.58	7.93	3.18	3.18

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp