

Non-Catalog Model

Power Splitter/Combiner

2 Way-0°

ZAPD-4-13



CASE STYLE: F14

Important Note

This is a non-catalog model and can be manufactured on specific request. Pricing and delivery information can be supplied upon request.

Please click "Back", and then click "Contact Us" for Applications support.

ELECTRICAL SPECIFICATIONS 50Ω@

Parameter	Min.	Typ.	Max.	Units
Frequency	2.0		4.2	GHz
Isolation	19			dB
Insertion Loss Above 3.0 dB			0.8	dB
Phase Unbalance			6	deg.
Amplitude Unbalance			0.4	dB
Power Rating			10	W
Internal Load Dissipation			0.125	W


MAXIMUM RATINGS

Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS

SUM PORT	S	N Male
PORT 1	1	N Female
PORT 2	2	N Female

Electrical Schematic



Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

REV. OR
M117878
ZAPD-4-13
080522