

Coaxial

Power Splitter/Combiner

2 Way-0° 50Ω 2000 to 4200 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	10W max.
Internal Dissipation	0.125W max.

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
2.00	2.00	.75	1.00	.25	1.500	.125
50.80	50.80	19.05	25.40	6.35	38.10	3.18

H	J	K	L	wt
.39	1.00	.50	1.00	grams
9.91	25.40	12.70	25.40	170.0

Features

- wideband, 2000 to 4200 MHz
- low insertion loss, 0.4 dB typ.
- good isolation, 25 dB typ.
- up to 10W power input as splitter
- excellent amplitude unbalance, 0.1 dB typ.
- excellent phase unbalance, 0.5 deg. typ.
- rugged shielded case

Applications




- MMDS
- ISM
- wireless
- communication systems
- instrumentation

Splitter Electrical Specifications


FREQ. RANGE (MHz)	ISOLATION (dB)	INSERTION LOSS (dB) ABOVE 3.0 dB	PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)
f_L - f_U	Typ. Min	Typ. Max.	Max.	Max.
2000-4200	25 19	0.4 0.8	6	0.4

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1 S-2						
2000.00	3.29 3.28	0.01	21.06	0.12	1.33	1.10	1.10
2055.00	3.32 3.32	0.00	21.81	0.06	1.32	1.11	1.11
2165.00	3.36 3.36	0.00	23.52	0.02	1.28	1.12	1.12
2275.00	3.28 3.28	0.01	25.26	0.06	1.26	1.12	1.13
2385.00	3.26 3.26	0.01	27.29	0.06	1.25	1.14	1.16
2550.00	3.21 3.22	0.01	30.80	0.03	1.23	1.16	1.19
2715.00	3.26 3.26	0.00	34.52	0.07	1.22	1.15	1.20
2880.00	3.27 3.27	0.01	35.28	0.11	1.24	1.19	1.25
3100.00	3.19 3.19	0.01	31.23	0.05	1.23	1.20	1.27
3320.00	3.30 3.28	0.02	28.17	0.13	1.25	1.22	1.28
3540.00	3.25 3.23	0.02	26.28	0.06	1.20	1.21	1.26
3760.00	3.31 3.28	0.02	25.49	0.06	1.16	1.15	1.20
3980.00	3.27 3.24	0.04	25.51	0.02	1.10	1.13	1.17
4090.00	3.16 3.12	0.03	25.74	0.04	1.09	1.10	1.15
4200.00	3.27 3.24	0.04	25.99	0.02	1.10	1.08	1.13



electrical schematic



N-Type version shown

CASE STYLE: F14

Connectors	Model	Price	Qty.
N-TYPE	ZAPD-4-N(+)	\$59.95	(1-9)
SMA	ZAPD-4-S(+)	\$59.95	(1-9)

+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

REV. A
M98898
ZAPD-4
HY/TD/CP/AM
070202