

Power Splitter/Combiner with amplifier

2 Way-0°

ZAPD-ED10492A/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-929

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		1090		1900 MHz
Isolation	1090 - 1900 MHz		35	dB
Gain	1090 - 1900 MHz		3.80	dB
Amplitude Unbalance	1090 - 1900 MHz		0.06	dB
VSWR	SUM Port		1.27	(:1)
	OUT Ports		1.11	(:1)
Noise Figure	1545-1605 MHz		3.00	dB
DC Power			4.5-5.5	V

MAXIMUM RATINGS	
Operating Temperature	-5°C to 70°C
Storage Temperature	-5°C to 70°C

COAXIAL CONNECTIONS	
ANTENNA IN	J1
OUTPUT PROVIDING DC	J2
OUTPUT PROVIDING DC	J3, Right Angle

Functional Diagram

