25 dB DC Pass High Power Signal Tap ZARC-25-551-S+

100 to 550 MHz 50Ω 100W

The Big Deal

- High Power Handling, 100 W
- Excellent Mainline Loss, 0.15 dB typ.
- Very good VSWR, 1.2:1 typ.



CASE STYLE: AW1564

Product Overview

The ZARC-25-551-S+ high power signal tap is ideal for monitoring up to 100W signals in VHF and UHF applications. Overall dimensions are 3.00" x 2.81" x 2.03" high. The rugged aluminum alloy case features stainless steel SMA connectors and an anodized aluminum heat sink, enclosing a welded module for reliable, long-term performance.

Feature	Advantages
0.15 dB typ. mainline loss	Extremely low internal power dissipation, reducing mainline loss and internal temperature for high reliability
VSWR 1.2:1 typ	Very good 50 Ω impedance matching minimizes interference with signal integrity
±0.5 dB coupling flatness	Provides highly accurate sampling of signal power
DC Pass up to 3A	Suitable for applications using remote antenna control or other remote motorized requirements
100 W input maximum	High power capacity, combined with excellent insertion loss and VSWR, supports operation in transmitters and base stations for amateur radio, PMR, TV, maritime, aviation, and military applications

Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collective), "Standard Terms"), Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



25 dB DC Pass High Power Signal Tap ZARC-25-551-S+

50Ω

100 to 550 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input	100W max.
DC Current (IN-OUT)	ЗA
Permanent damage may occur if any of the	hese limits are exceeded.

100W

Coaxial Connections

INPUT	1
OUTPUT	2
COUPLED	3

Outline Drawing



Outline Dimensions (inch) в С D A 3.00 F G 2.03 2.06 .10 2,500 1.525 .125 76.20 52.32 51.56 63.50 2.54 38.74 3.18 н Κ Μ Ν wt 2.00 .50 .50 .50 1.00 2.00 grams 12.70 12.70 12.70 25.40 50.80 50.80 230

Electrical Schematic COUPLER

COUPLED

ZARC-25-551-S+

MAINLINE LOSS

250 300 350 400

FREQUENCY (MHz)

DC+RF

450 500 550

DC+RF INPUT

0.3

MAINLINE LOSS (dB) 0.1

0.0

100 150 200

Notes

Features

- excellent mainline loss, 0.15 dB typ.
- good VSWR, 1.2 typ.

Applications

- instrumentation
- amateur radio



Generic photo used for illustration purposes only CASE STYLE: AW1564 Connectors Model ZARC-25-551-S+ SMA

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Electrical Specifications at 25°C


Parameter	Condition (MHz)	Min.	Тур.	Max.	Unit	
Frequency Range		100		550	MHz	
	100	—	0.06	0.20		
Mainline Loss (above theoretical 0.014 dB)	300	_	0.12	0.25	dB	
	550	_	0.18	0.30		
	100-550		25.5			
Coupling* (IN-CPL, OUT-CPL)	100	24.7	26.3	27.8	dB	
	300	24.0	25.8	27.6	uв	
	550	22.7	24.9	27.0		
Coupling Flatness(±)	100-300	—	0.3	0.6	dB	
	300-550	_	0.5	0.8	uв	
	100	24	32	—		
Return Loss (Input)	300	18	23	_	dB	
	550	16	20			
	100	24	33	—		
Return Loss (Output)	300	18	23	_	dB	
	550	16	20			
	100	12	13	_		
Return Loss (Coupling)	300 20 24 — d	dB				
	550	12	14			
Input Power	100-550	_	—	100	W	

* Coupling can be used for both forward and reversed direction.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)			Return Loss (dB)	
	In-Out	In-Cpl	Out-Cpl	In	Out	Cpl
100.00	0.05	26.50	26.47	34.80	35.47	14.51
200.00	0.08	26.21	26.07	28.80	29.55	24.20
300.00	0.11	25.94	25.66	25.41	26.27	24.68
400.00	0.14	25.56	25.11	23.63	24.72	19.64
500.00	0.16	24.96	24.38	22.91	24.21	16.31
512.00	0.16	24.86	24.28	22.87	24.21	15.98
520.00	0.16	24.80	24.20	22.85	24.24	15.76
530.00	0.17	24.71	24.11	22.84	24.27	15.50
540.00	0.17	24.62	24.01	22.86	24.31	15.24
550.00	0.17	24.53	23.90	22.86	24.37	14.98





A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

REV. B M171494 ED-14166/1 ZARC-25-551-S+ CH/CP/AM 200513 Page 2 of 2

,,,,)Mini-Circuits