# Absorptive DT RF Switch

DC<sup>2</sup> - 5000 MHz 500

# **The Big Deal**

- Wide bandwidth DC<sup>2</sup> to 5000 MHz
- High Isolation, 70 dB typ.
- Very fast switching, 20ns typ.
- Low video break thru 45 mVp-p typ.



ZASWA2-50DR-FA+

CASE STYLE: CY1481

# **Product Overview**

The ZASWA2-50DR-FA+ is an excellent high isolation, solid state SPDT, absorptive RF switch. With its broad frequency range, fast switching time and excellent RF performance, the ZASWA2-50DR-FA+ is an excellent replacement for the Mini-Circuits' legacy switch model ZASWA2-50DR-FT+. Refer app note AN-80-022 for more details. The wide bandwidth, high isolation and fast switching characteristics makes this switch a versatile choice for several RF applications & systems.

# **Key Features**

Feature	Advantages
Integrated TTL Driver	-Operates at +5V to -5V -Low control current allows compatibility with a variety of driver circuits -Fast 20 ns typ.Switching time
Excellent for a Variety of Applications From Bench to Integrated Systems	-High speed testers -Automated switching networks -Wireless Infrastructure -Military
Excellent RF Performance	-Wide bandwidth: DC <sup>2</sup> to 5000 MHz -Good Insertion Loss: 2.5 dB Typ -Low video leakage, 45 mVp-p typ.

2. All RF connections must be blocked or held at 0V DC. Low frequency is determined by value of Coupling capacitors at RF ports.

- A. B.
- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Notes

# Absorptive **SPDT RF Switch**

Absorptive RF Switch with Internal Driver Dual Supply Voltage, +5V & -5V

### **Product Features**

- Wide bandwidth, DC<sup>2</sup> to 5000 MHz
- Good Insertion loss, 2.5 dB typ.
- Internal TTL driver
- Fast switching, Rise/fall time, 4 ns typ.
- Wide operating temperature, -20°C to +85°C





# ZASWA2-50DR-FA+

CASE STYLE: CY1481

Model Connectors SMA ZASWA2-50DR-FA+

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


### **Typical Applications**

- Cellular
- ISM, WCDMA, WIMAX
- PCN
- Automated switching networks
- Military

### **General Description**

The ZASWA2-50DR-FA+ is a 50Ω absorptive, high isolation, SPDT RF switch. It is designed for RF/wireless applications covering a broad frequency range from DC<sup>2</sup> to 5000 MHz with good insertion loss and Isolation. The ZASWA2-50DR-FA+ operates with a dual supply voltage ±5V. This unit includes an internal driver circuitry which makes it easier to control switching with standard voltage levels.

## Schematic and Application Circuit



2. All RF connections must be blocked or held at 0V DC. Low frequency is determined by value of Coupling capacitors at RF ports

#### Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collective), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



REV. OR M168831 ZASWA2-50DR-FA+ AD/CP/AM 200522 Page 2 of 5

### RF Electrical Specifications, DC<sup>2</sup> - 5000 MHz, T<sub>AMB</sub>=25°C, Supply Voltage (+V, -V) =+5V, -5V

Parameter	Condition (MHz)	Min.	Тур.	Max.	Units	
Frequency Range		DC <sup>2</sup>		5000	MHz	
	DC <sup>2</sup> -100	_	1.3	2.0	dB	
	100-1000	_	1.7	2.5		
Insertion Loss	1000-2000	_	1.8	3.0		
	2000-5000	_	3.0	4.5		
	DC <sup>2</sup> -100	68	90	_	dB	
Isolation between Common port and RF1/RF2 Ports	100-1000	75	90	—		
	1000-2000	65	82	—		
Return Loss (IN PORT)	2000-5000 DC <sup>2</sup> -5000	40	65 14		dB	
	DC <sup>2</sup> -5000		14.5		dB	
Return Loss @ RF1/RF2 ports (ON STATE)						
Return Loss @ RF1/RF2 ports (OFF STATE)	DC <sup>2</sup> -5000 DC2-100		16.5		dB	
		_	-	—		
Input 1dB Compression (1)	100-1000	_	>20	_	dBm	
	1000-2000 2000-5000	_	>24 >23	_		
DC	Electrical Specification	S	1	1	1	
Supply Voltage (+V)		_	5	_	V	
Supply Voltage (-V)		_	-5	_	V	
Positive Supply Current	+V=5V	_	4.6	_	mA	
Negative Supply Current	-V=-5V	_	-8.2	—	mA	
Control Voltage Low		0	—	0.7	V	
Control Voltage High		2.1	—	5	V	
Control Current		—	-	2	mA	
S	witching Specifications					
Rise/Fall Time (10 to 90% or 90 to 10% RF)	+V=5V, -V=-5V	_	5	_	nSec	
Switching Time (50% CTRL to 90/10% RF)	+V=5V, -V=-5V	_	20	_	nSec	
Video Feed through (Control 0-5V, Frequency 1 MHz)	+V=5V, -V=-5V	_	45	_	mV <sub>P-P</sub>	

1. At low frequency(<100 MHz), the dynamic range of switch decreases.

#### **Absolute Maximum Ratings**

Parameter	Ratings
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
Supply Voltage (+V <sub>DD</sub> & -V <sub>DD</sub> )	+5.5V, -5.5V
Voltage Control	-0.2V min, +5.5V max
RF input power <sup>3</sup>	31 dBm
ESD, HBM	Class 1A (250 to <500V) per JESD22-A114

2. All RF connections must be blocked or held at 0V DC. Low frequency is determined by value of Coupling capacitors at RF ports. 3 Frequency range of 500-5000 MHz.

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




# **SPDT RF Switch**

#### Truth Table (State of control voltage selects the desired switch state)

State of Control Voltorio	Switch State - RF IN to			
State of Control Voltage	RF1	RF2		
Low	ON	OFF		
High	OFF	ON		
ON- low insertion loss state OFF- Isolation State				

# **Coaxial Configuration**



#### **Coaxial Connections**


Function	Port Number	Description
RF IN	1	RF Common/ SUM Port
RF1	3	RF Out #1/In Port #1
RF2	6	RF Out #2/In Port #2
Control	4	TTL Control IN
+5V	2	Positive Supply Voltage
-5V	5	Negative Supply Voltage
Gnd	Gnd	Ground

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



# ZASWA2-50DR-FA+

# **Outline Drawing (CY1481)**



	Outline Dimensions (inch )							
J	н	G	F	E	D	С	В	Α
.250	.62	.75	2.620	.31	.69	1.50	2.00	3.24
6.35	15.75	19.05	66.55	7.87	17.53	38.10	50.80	82.30
wt	S	R	Q	Р	Ν	М	L	K
grams	1.00	.52	.10	1.00	.50	.31	.50	.25
80.0	25.40	13.21	2.54	25.40	12.70	7.87	12.70	6.35

## **Additional Detailed Technical Information**

Additional information is available on our web site. To access this information enter the model number on our web site home page.			
	Data Table		
Performance Data	Swept Graphs		
	S-Parameter (S2P Files) Data Set (.zip file)		
Case Style CY1481			
Environmental Ratings ENV28T16			

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

