

Power Splitter/Combiner

16 Way-0°

ZB16PD-ED7000/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : UU573

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		300		800 MHz
Isolation	300 - 800 MHz		23	
Insertion Loss Above 12.0 dB	300 - 800 MHz		0.70	
Phase Unbalance	300 - 800 MHz		4.815	
Amplitude Unbalance	300 - 800 MHz		0.531	
VSWR	SUM Port		1.30	(:1)
	OUT Ports		1.10	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

Functional Diagram

