

Power Splitter/Combiner

ZB2PD-ED13650

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : AW254

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		60		660 MHz
Isolation			30	dB
Insertion loss above 3 dB	60-660 MHz		0.50	dB
Phase Unbalance	60-660 MHz		0.60	Deg
Amplitude Unbalance	60-660 MHz		0.05	dB
VSWR	SUM Port		1.13	(:1)
	OUT Ports		1.12	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 90°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2

Functional Diagram

