

Power Splitter/Combiner

ZB3PD2-ED13401

3 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : 99-01-1332

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		350		6160 MHz
Isolation	350-6160 MHz		23	dB
Insertion Loss Above 4.8 dB	350-6160 MHz		1.00	dB
Phase Unbalance	350-6160 MHz		3.86	deg.
Amplitude Unbalance	350-6160 MHz		0.40	dB
VSWR	SUM Port		1.32	(:1)
	OUT Ports		1.41	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3

Functional Diagram

