

Coaxial


SMA Fixed Attenuator

50Ω 1W 4dB DC to 6000 MHz

Maximum Ratings

Operating Temperature	-45°C to 100°C
Storage Temperature	-55°C to 100°C

Outline Drawing



Outline Dimensions (inch/mm)

B	D	E	wt
.410	1.43	.312	grams
10.41	36.32	7.92	10.0


Features

- wideband coverage, DC to 6000 MHz
- 1 watt rating
- rugged unibody construction
- off-the-shelf availability
- very low cost

Applications

- impedance matching
- signal level adjustment

VAT-4+
VAT-4



CASE STYLE: FF704

Connectors	Model	Price	Qty.
SMA	VAT-4(+)	\$11.95 ea.	(1-9)

+ RoHS compliant in accordance
with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site
for RoHS Compliance methodologies and qualifications.

Electrical Specifications



FREQ. RANGE (MHz)	ATTENUATION * (dB) Flatness **					VSWR (:1)					MAX. INPUT POWER (W)
	DC-3 GHz	3-5 GHz	5-6 GHz	DC-6 GHz		DC-3 GHz	3-5 GHz	5-6 GHz			
f _L -f _U	Nom.	Typ.	Typ.	Typ.	Typ.	Typ.	Max.	Typ.	Max.	Typ.	
DC-6000	4±0.3	0.20	0.15	0.20	0.55	1.05	1.20	1.15	1.45	1.45	1.0

* Attenuation varies by 0.3 dB max. over temperature.

** Flatness= variation over band divided by 2.

Typical Performance Data

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
0.03	4.06	1.01
50.00	4.01	1.00
100.00	4.02	1.01
500.00	4.09	1.03
1000.00	4.15	1.05
2000.00	4.27	1.05
3000.00	4.40	1.03
4000.00	4.51	1.10
5000.00	4.68	1.22
6000.00	5.15	1.41



designers kit available

Kit No.	No. of Units in Kit	Description	Price \$ per Kit
K1-VAT	5	1 of ea. VAT-3(+), 6(+), 10(+), 20(+), 30(+)	49.95
K2-VAT	10	1 of ea. VAT-1(+), 2(+), 3(+), 4(+), 5(+), 6(+), 7(+), 8(+), 9(+), 10(+)	99.95
K3-VAT	6	2 of ea. VAT-3(+), 6(+), 10(+)	59.95

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

REV. E
ED-105218
VAT-4
LC/TD/CP/AM
060829