# **SMA Fixed Attenuator**

DC to 6000 MHz **1W** 5dB  $50\Omega$ 

# **Maximum Ratings**

Operating Temperature -45°C to 100°C Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded

#### **Features**

- wideband coverage, DC to 6000 MHz
- 1 watt rating
- rugged unibody construction
- · off-the-shelf availability
- · very low cost

#### **Applications**

- impedance matching
- · signal level adjustment



Generic photo used for illustration purposes only

CASE STYLE: FF704 Connectors Model


SMA

+RoHS Compliant

VAT-5+

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### **Outline Drawing**



# Outline Dimensions (inch )

wt	Е	D	В
grams	.312	1.43	.410
10.0	7.92	36.32	10.41

# **Electrical Specifications**


FREQ. RANGE (MHz)		ATTENUATION * (dB) Flatness **			VSWR (:1)		MAX. INPUT POWER		
		DC-3 GHz	3-5 GHz	5-6 GHz	DC-6 GHz	DC-3 GHz	3-5 GHz	5-6 GHz	(W)
f <sub>L</sub> -f <sub>U</sub>	Nom.	Тур.	Тур.	Тур.	Тур.	Тур. Мах.	Тур. Мах.	Тур.	
DC-6000	5±0.3	0.10	0.10	0.10	0.25	1.05 1.20	1.15 1.45	1.40	1.0


Attenuation varies by 0.3 dB max. over temperature.


# **Typical Performance Data**

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
0.03	4.98	1.00
50.00	4.97	1.00
100.00	4.98	1.00
500.00	5.03	1.01
1000.00	5.06	1.02
2000.00	5.11	1.01
3000.00	5.17	1.03
4000.00	5.22	1.11
5000.00	5.30	1.24
6000.00	5.44	1.40

#### **Electrical Schematic**







A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement ins.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively: "Standard Terms"): Purchases of this part. Ferrormance and updany authorities and contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

<sup>\*\*</sup> Flatness= variation over band divided by 2.