

Engineering Development Model

Power Splitter/Combiner

ZB4PD-ED10317/1

4 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : UU188

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		460		2000 MHz
Isolation	460 - 2000 MHz		25	dB
Insertion Loss Above 6.0 dB	460 - 2000 MHz		0.50	dB
Phase Unbalance	460 - 2000 MHz		13.801	deg.
Amplitude Unbalance	460 - 2000 MHz		0.091	dB
VSWR	SUM Port		1.30	(:1)
	OUT Ports		1.35	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4

Functional Diagram

