# **SMA Fixed Attenuator**

Generic photo used for illustration purposes only

CASE STYLE: FF704 Connectors Model SMA

VAT-9+

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


### DC to 6000 MHz $50\Omega$ **1W** 9dB

# **Maximum Ratings**

Operating Temperature -45°C to 100°C Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded

# **Outline Drawing**



# Outline Dimensions (inch )

В D Ε wt .410 .312 grams 1.43 10.41 36.32 7.92 10.0

### **Features**

- wideband coverage, DC to 6000 MHz
- 1 watt rating
- rugged unibody construction
- · off-the-shelf availability
- · very low cost

## **Applications**

- impedance matching
- · signal level adjustment

# **Electrical Specifications**


FREQ. RANGE (MHz)	ATTENUATION * (dB) Flatness **				VSWR (:1)			MAX. INPUT POWER	
		DC-3 GHz	3-5 GHz	5-6 GHz	DC-6 GHz	DC-3 GHz	3-5 GHz	5-6 GHz	(W)
f <sub>L</sub> f <sub>U</sub>	Nom.	Тур.	Тур.	Тур.	Тур.	Тур. Мах.	Тур. Мах.	Тур.	
DC-6000	9±0.3	0.10	0.10	0.10	0.10	1.05 1.20	1.15 1.50	1.45	1.0


Attenuation varies by 0.3 dB max. over temperature.


# **Typical Performance Data**

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
0.03	9.01	1.00
50.00	9.00	1.00
100.00	9.01	1.00
500.00	9.05	1.00
1000.00	9.08	1.00
2000.00	9.09	1.03
3000.00	9.08	1.08
4000.00	9.03	1.16
5000.00	9.00	1.29
6000.00	8.92	1.45

## **Electrical Schematic**







A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement ins.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively: "Standard Terms"): Purchases of this part. Ferrormance and updany authorities and contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

<sup>\*\*</sup> Flatness= variation over band divided by 2.