

4 Way-0° 50Ω 850 to 930 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	10W max.
Internal Dissipation	0.375W max.
DC Current	2.0 A (500mA for each port)
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4

Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F
3.50	2.13	.88	.150	3.350	1.06
88.90	54.10	22.35	3.81	85.09	26.92
G	H	J	K	wt	
.125	1.75	.44	.89	grams	
3.18	44.45	11.18	22.61	260	

Features

- high isolation, 30 dB typ.
- rugged shielded case
- very good VSWR, 1.10:1 typ.
- up to 10W power input as a splitter

Applications

- cellular
- communication systems
- receivers/transmitters

SMA version shown
CASE STYLE: UU188

Connectors	Model
SMA	ZB4PD1-930-S
N-TYPE	ZB4PD1-930-N

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 6.0 dB		PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)	VSWR (:1)			
f_L - f_U	Typ.	Min.	Typ.	Max.	Max.	Max.	S Typ.	S Max.	OUT Typ.	OUT Max.
850-930	30	20	0.3	0.5	5	0.25	1.10	1.25	1.09	1.25


Typical Performance Data

Freq. (MHz)	Total Loss ¹ (dB)				Amp. Unbal. (dB)	Isolation (dB)			VSWR S	VSWR 1	VSWR 2	VSWR 3	VSWR 4
	S-1	S-2	S-3	S-4		1-2	2-3	3-4					
850.00	6.14	6.11	6.10	6.13	0.04	28.39	33.26	27.78	1.01	1.10	1.06	1.06	1.10
857.44	6.13	6.09	6.10	6.09	0.04	29.23	34.16	28.57	1.01	1.10	1.06	1.05	1.10
862.31	6.16	6.12	6.11	6.12	0.05	29.70	34.73	28.96	1.02	1.10	1.06	1.05	1.10
867.19	6.12	6.10	6.11	6.09	0.04	30.23	35.31	29.44	1.02	1.09	1.06	1.05	1.09
876.94	6.15	6.12	6.13	6.11	0.03	30.97	36.38	30.21	1.03	1.09	1.05	1.04	1.09
885.06	6.10	6.09	6.08	6.08	0.03	31.29	36.88	30.57	1.04	1.09	1.05	1.04	1.09
886.69	6.13	6.10	6.09	6.09	0.04	31.31	37.08	30.60	1.04	1.09	1.05	1.04	1.09
891.56	6.10	6.09	6.08	6.07	0.03	31.38	37.36	30.70	1.04	1.08	1.04	1.04	1.08
899.69	6.09	6.08	6.08	6.06	0.03	31.11	37.41	30.49	1.05	1.08	1.04	1.03	1.08
907.00	6.08	6.08	6.07	6.05	0.03	30.52	37.21	30.42	1.06	1.08	1.04	1.03	1.08
911.88	6.06	6.06	6.08	6.06	0.02	30.19	36.93	29.68	1.07	1.08	1.03	1.03	1.08
920.00	6.06	6.07	6.07	6.04	0.03	29.34	36.13	28.90	1.08	1.07	1.03	1.03	1.07
924.88	6.06	6.07	6.09	6.04	0.05	28.82	35.64	28.37	1.09	1.07	1.03	1.03	1.07
927.31	6.07	6.05	6.06	6.03	0.04	28.52	35.30	28.12	1.09	1.07	1.03	1.03	1.07
930.00	6.06	6.07	6.07	6.03	0.05	28.22	35.11	27.88	1.10	1.07	1.03	1.03	1.07

1. Total Loss = Insertion Loss + 6dB splitter loss.



electrical schematic



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

