# Bandpass Filter

**VBF-1945+** 

50Ω 1850 to 2040 MHz

## **The Big Deal**

- Low Insertion Loss (2.0 dB typical)
- Good close-in rejection
- Versatile small size, coaxial, 1.43" length



CASE STYLE: FF704

## **Product Overview**

The VBF-1945+ Band Pass Filter is constructed using internal LTCC Band Pass Filter structure to achieve repeatable performance. Covering 1945 MHz  $\pm$  95 MHz, these units offer low insertion loss and good rejection at the band reject edges. Built using Mini-Circuits proven unibody construction which integrates the RF connectors with the case body, the VBF-1945+ takes very little space and meets rugged test lab system environment.

## **Key Features**

Feature	Advantages	
Good Rejection close to pass band	Provides good rejection of signals close to the pass band, for improved system performance.	
Compact Versatile Case (1.43"x0.41")	Enables use in a variety of applications including space constrained connectorized systems.  Connectors: SMA Female (1), SMA Male (1)	
Rugged Unibody Construction	Mini-Circuits Unibody construction allows survivability in critical applications including militarized or industrial systems.	

#### Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.ninicircuits.com/MCLStore/terms.jsp

# **Bandpass Filter**

#### $50\Omega$ 1850 to 2040 MHz

#### **Maximum Ratings**

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	1.5W max_at 25°C

<sup>\*</sup>Passband rating, derate linearly to 0.25W at 100°C ambient

## **Features**

- · Small size
- Temperature stable

**Applications** 

Pass Band

Stop Band, Lower

Stop Band, Upper

· Rugged unibody construction

**Parameter** 

CASE STYLE: FF704

VBF-1945+

Connectors	Model
SMA	VBF-1945+

#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Тур.

20

25

25

Max.

3.0

2.5

Unit

MHz

dB

:1


dB


٠1

dB

#### • Harmonic Rejection • Transmitters / Receivers

## **Outline Drawing**





Center Frequency

Insertion Loss


Insertion Loss


Insertion Loss

**VSWR** 

**VSWR** 

**VSWR** 





### Outline Dimensions (inch)

	E	D	В
gra	.312	1.43	.410
1	7.92	36.32	10.41

### Typical Performance Data at 25°C

Electrical Specifications at 25°C

F1-F2

F1-F2

DC-F3

DC-F3

F4-F5

F4-F5

Frequency (MHz)

1850-2040

1850-2040


DC-1500


DC-1500


3600-5700

3600-5700

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
0.30	67.55	3349.77
300.00	29.47	107.34
1000.00	35.80	69.99
1400.00	52.82	46.90
1550.00	23.37	28.71
1800.00	2.50	1.58
1850.00	2.02	1.58
1900.00	1.88	1.69
2040.00	1.76	1.29
2200.00	5.25	5.68
2500.00	13.24	27.99
2900.00	20.02	53.43
4500.00	46.92	47.55
4900.00	37.86	44.11
5700.00	32.47	27.83







- OBS

  Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
  Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
  The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

Permanent damage may occur if any of these limits are exceeded.