


Engineering Development Model

Power Splitter/Combiner ZB4PD1-ED12789/1

4 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-847

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		500		2400 MHz
Isolation	500 - 2400 MHz		22	dB
Insertion Loss Above 6.0 dB	500 - 2400 MHz		0.40	dB
Phase Unbalance	500 - 2400 MHz		1.851	deg.
Amplitude Unbalance	500 - 2400 MHz		0.027	dB
VSWR	SUM Port		1.30	(:1)
	OUT Ports		1.20	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

Functional Diagram

