# **Bandpass Filter**

**VBF-7331+** 

6850 to 7850 MHz  $50\Omega$ 

# The Big Deal

- Good rejection
- Good VSWR
- Connectorized package



Generic photo used for illustration purposes only CASE STYLE: FF704

## **Product Overview**

The VBF-7331+ Band Pass Filter is constructed using internal LTCC Band Pass Filter structure to achieve repeatable performance. This offers low insertion loss and good rejection at the band reject edges. Built using Mini-Circuits proven unibody construction which integrates the RF connectors with the case body, the VBF-7331+ takes very little space and meets rugged test lab system environment.

# **Key Features**

Feature	Advantages		
Good Rejection close to pass band	Provides good rejection of signals close to the pass band, for improved system performance.		
Compact Versatile Case (1.43"x0.41")	Enables use in a variety of applications including space constrained connectorized systems.  Connectors: SMA Female (1), SMA Male (1)		
Rugged Unibody Construction	Mini-Circuits Unibody construction allows survivability in critical applications including militarized or industrial systems.		

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

**Features** 

Small size

• Temperature stable

**Applications** · Harmonic rejection • Transmitters / Receivers • UWB impulse radar · Emission masking

• Rugged unibody construction

# **Bandpass Filter**

 $50\Omega$ 6850 to 7850 MHz

# VBF-7331+



Generic photo used for illustration purposes only CASE STYLE: FF704
Connectors Model

VBF-7331+

Connectors SMA


Electrical Specifications at 25°C							
Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Insertion Loss	F1	7331	-	-	2	dB
Pass Band	Pass Band Insertion Loss VSWR		6850 - 7850	-	1.4	-	dB
			6850 - 7850	-	1.45	-	:1
	Insertion Loss	DC-F4	10-5600	10	23	-	dB
Stop Band, Lower		F4-F5	5600-5800	-	10	-	dB
	VSWR		10-5800	-	20	-	:1
	Insertion Loss	F6-F7	9300 - 10500	10	20	-	dB
Stop Band, Upper		F7-F8	10500-13300	-	10	-	dB
	VSWR	F6-F8	9300-13300	-	20	-	:1

(1) In Application where DC voltage is present at either input or output ports, coupling capacitors are required.


Maximum Ratings				
Operating Temperature	-55°C to 100°C			
Storage Temperature	-55°C to 100°C			
RF Power Input	2.5 W max.			

\*Passband rating, derate linearly to 0.7 W at 100°C ambient Permanent damage may occur if any of these limits are exceeded.

# **Functional Schematic**




### **Typical Frequency Response**




+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
10	76.27	7226.80	6850	0.46
200	69.65	262.08	6900	0.45
900	44.13	118.17	6950	0.45
2150	30.09	84.25	7000	0.44
3000	25.06	77.66	7050	0.44
3700	22.00	67.17	7100	0.44
4250	20.12	55.05	7150	0.44
5600	30.34	20.53	7200	0.44
5800	16.15	12.98	7250	0.44
6250	3.07	2.37	7331	0.44
6850	1.38	1.28	7350	0.44
7331	1.43	1.40	7400	0.44
7850	1.78	1.10	7450	0.44
8600	13.90	8.34	7500	0.45
9300	25.50	18.83	7550	0.46
10000	24.67	23.10	7600	0.46
10500	28.52	24.93	7650	0.47
11400	14.97	12.91	7700	0.48
12100	28.03	25.93	7750	0.50
13300	29.93	23.48	7850	0.53





Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.js;

### **Coaxial Connections**

PORT - 1	SMA-MALE
PORT - 2	SMA-FEMALE

### **Outline Drawing**



## Outline Dimensions (inch )

wt.	Е	D	В
grams	.312	1.43	.410
10	7 92	36.32	10.41

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp