

Band Pass Filter

VBFZ-EDR8450U

Coaxial SMA

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : FF1145

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Passband (Loss < 2 dB)	1800		2250	MHz
Center Frequency		2025		MHz
Stopband Low Band (Loss > 20 dB)	DC		1290	MHz
High Band (Loss > 20 dB)	2900		18500	MHz
Passband VSWR		1.4		(:1)
Stopband VSWR		18		(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	7W at 25°C

Functional Schematic

