

Engineering Development Model

Power Splitter/Combiner ZB8PD-ED10613C/1 8 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



SMA version shown

CASE STYLE : Z41

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	6500		8800	MHz
Isolation 6500-8800 MHz		31		dB
Insertion Loss Above 9.0 dB 6500-8800 MHz		1.00		dB
Phase Unbalance 6500-8800 MHz		5.75		deg.
Amplitude Unbalance 6500-8800 MHz		0.45		dB
VSWR	SUM Port	1.26		(:1)
	OUT Ports	1.22		(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4
PORT 5	5
PORT 6	6
PORT 7	7
PORT 8	8

Functional Diagram

