Coaxial **High Pass Filter**

50Ω

1220 to 4600 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	7W max.

* Passband rating, derate linearly to 3W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded

Features

- rugged unibody construction, small size
- 7 sections
- temperature stable
- excellent power handling, 7W
- · low cost

Applications

- sub-harmonic rejection
- transmitters/receivers
- lab use

VHF-1200+




Generic photo used for illustration purposes only

CASE STYLE: FF704 Connectors Model SMA VHF-1200+

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing



Outline Dimensions (inch)


В	D	Е	wt
.410	1.43	.312	grams
10.41	36.32	7.92	10.0

Electrical Specifications (T_{AMB}=25°C) PASSBAND (MHz) STOP BAND fco, MHz **VSWR** (:1) NO. OF (MHz) SECTIONS Nom. Тур. Min Frequency (MHz) (loss 3 dB) (loss < 1.3 dB) (loss < 2 dB)(loss > 40 dB)(loss > 20 dB)Тур. Max Тур. Stopband 1.5:1 910 1180 1300-3200 750 1380-4000 1220-4600 20:1 7

typical frequency response


40dB **ATTENUATION** 20dB 3dB Fco F 1.3dB FREQUENCY

electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1	104.60	1737.18
500	77.89	124.09
750	49.00	56.04
910	29.02	32.18
1050	13.46	12.18
1130	5.97	4.39
1180	3.08	2.29
1220	1.98	1.62
1300	1.24	1.39
1380	0.97	1.39
3200	0.46	1.43
4000	1.04	2.29
4600	1.72	3.14
7000	4.66	7.56
VHF-1200		VHF-1200
INSERTION LOSS	10000	VSWR



0 1000 2000 3000 4000 5000

FREQUENCY (MHz)

Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp

REV. H M151777 VHF-1200 EDR-6713/2 RVN/AD/AM 200520 Page 1 of 1

6000 7000

Mini-Circuits