

Engineering Development Model

Power Splitter/Combiner

ZB8PD-ED6107

8 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : Z41

ELECTRICAL SPECIFICATIONS 75Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		622		2500	MHz
Isolation	622 - 2500 MHz		27		dB
Insertion Loss Above 9.0 dB	622 - 2500 MHz		0.84		dB
Amplitude Unbalance	622 - 2500 MHz		0.272		dB
VSWR	SUM Port		1.60		(:1)
	OUT Ports		1.14		(:1)

Note: Denotes 75 Ohm model, for coax connector models 75 Ohm BNC connectors are standard.

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4
PORT 5	5
PORT 6	6
PORT 7	7
PORT 8	8

Functional Diagram

