

50Ω DC to 400 MHz

The Big Deal

- Excellent power handling, 3.5W
- Temperature stable
- Rugged, unibody construction
- Good rejection, 31 dB typical

VLFG-400+



Generic photo used for illustration purposes only CASE STYLE: FF704

Product Overview

VLFG-400+ is a 50 Ω low pass filter built in rugged unibody construction. Covering DC-400 MHz bandwidth, these units offer good matching within the passband and high rejection in stopband. VLFG-400+ offer low insertion loss, and excellent power handling capability. It handles up to 3.5W RF input power and provides a wide operating temperature range from -55°C to 125°C.

Key Features

Feature	Advantages		
Low passband insertion loss	Suitable for high performance application.		
3.5W Power handling	Supports a range of system power requirements.		
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.		

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Low Pass Filter

50 Ω DC to 400 MHz


Features

- Low loss, 1 dB typical
- Good rejection 31 dB typical
- Excellent power handling, 3.5 W
- Temperature stable
- Connectorized package


Applications

- Harmonic Rejection
- VHF/UHF transmitters / receivers
- RF suppression for DC lines on PCB
- Anti-aliasing for A/D converter

Functional Schematic



Typical Frequency Response







Generic photo used for illustration purposes only CASE STYLE: FF704

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Pa	rameter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Insertion Loss	DC-F1	DC - 400	—	1.0	1.8	dB
Pass Band	Freq. Cut-Off	F2*	520	_	3.0	—	dB
	Return Loss	DC-F1	DC - 400	_	18	—	dB
Cton Dand	Rejection Loss	F3-F4	800 - 2500	25	31	_	dB
Stop Band		E4-E5	2500 - 4500	_	23	_	dB


In Application where DC voltage is present at either input or output port, DC blocks are required. * Typically, a $\pm 5\%$ frequency deviation from the stated value may occur on a unit-to-unit basis.

Maximum Ratings				
Operating Temperature	-55°C to 125°C			
Storage Temperature	-55°C to 125°C			
RF Power Input*	3.5 W max.@25°C			
Peesband rating, derate linearly to 0.6 W at 125°C ambient				

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

	Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	
	10	0.12	36.88	
	50	0.20	32.49	
	100	0.27	29.81	
	200	0.42	27.20	
	400	0.96	20.67	
	500	2.14	10.48	
	520	2.71	8.72	
	530	3.07	7.92	
	645	20.16	2.48	
	705	30.86	1.78	
	800	34.73	1.31	
	900	37.41	0.97	
	1000	52.52	0.74	
	1500	39.81	0.38	
	2000	41.77	0.34	
	2500	34.41	0.33	
	3000	32.54	0.33	
	3500	32.10	0.33	
	4000	28.67	0.37	
	4500	49.60	0.36	



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits


www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.A ECO-013807 VLFG-400+ EDU3698 URJ 220627 Page 2 of 3

Coaxial Connections

PORT - 1	SMA-Male
PORT - 2	SMA-Female

Outline Drawing



Outline Dimensions (inch)

В	D	Е	wt.
.410	1.43	.312	grams
10.41	36.32	7.92	10

Note: Please refer to case style drawing for details

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's trandard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits