

Engineering Development Model

Power Splitter/Combiner

ZC24PD-ED15112502

24 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CONNECTOR: MMCX Female

CASE STYLE: 99-01-2104

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	2000		6000	MHz
Isolation		16		dB
Insertion Loss Above 13.8dB		2.2		dB
Phase Unbalance		10.0		deg.
Amplitude Unbalance		1.00		dB
VSWR	SUM Port	1.55		(:1)
	OUT Ports	1.35		(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2
.	.
.	.
.	.
PORT 24	24

