



Mini-Circuits

LTCC COAXIAL

Low Pass Filter

VLFG-4400+

50Ω

DC to 4400 MHz SMA Male/Female

KEY FEATURES

- Low Insertion Loss, 1.6 dB Typ.
- Return Loss, 15 dB Typ.
- Stopband Rejection, 45 dB Typ.
- Rugged Unibody Construction
- Power Handling: 4.5 Watts



Generic photo used for illustration purposes only


APPLICATIONS

- 5G Applications
- Test and Measurement

PRODUCT OVERVIEW

VLFG-4400+ is a Low Pass filter with DC to 4400 MHz passband supporting a variety of applications. This model provides 1.6 dB typical insertion loss over a wide band due to its rugged unibody construction. VLFG-4400+ offers low insertion loss, and excellent power handling capability. It handles up to 4.5 W RF input power and provides a wide operating temperature range from -55°C to 125°C.

FUNCTIONAL DIAGRAM

ELECTRICAL SPECIFICATIONS¹ AT +25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	DC-F1	DC - 4400	—	1.6	2.1	dB
	Freq. Cut-Off ²	Fc	5200	—	3	—	dB
	Return Loss	DC-F1	DC - 4400	—	15	—	dB
Stopband	Rejection	F2-F3	6200 - 6700	20	40	—	dB
		F3-F4	6700 - 8800	35	45	—	
		F4-F5	8800 - 12200	25	34	—	
		F5-F6	12200 - 18000	—	23	—	

1. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.

2. Typical variation $\pm 5\%$


ABSOLUTE MAXIMUM RATINGS³

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power ⁴	4.5 W @+25°C

3. Permanent damage may occur if any of these limits are exceeded.

4. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 1 W at +125°C.

TYPICAL FREQUENCY RESPONSE AT +25°C



Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
ECO-026769
VLFG-4400+
EDU5164
URJ
250910

PAGE 1 OF 4



LTCC COAXIAL

Low Pass Filter

VLFG-4400+





Mini-Circuits

50Ω

DC to 4400 MHz

SMA Male/Female

TYPICAL PERFORMANCE GRAPHS AT +25°C






CONNECTOR DESCRIPTION

Function	Functionality	Connector
RF1	Port-1	SMA MALE
RF2	Port-2	SMA FEMALE

CASE STYLE DRAWING



Unit weight: 10.0grams

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm.04$ "; 3 Pl. $\pm.30$ "

PRODUCT MARKING*: VLFG-4400+

*Marking may contain other features or characters for internal lot control.



Mini-Circuits

LTCC COAXIAL

Low Pass Filter

VLFG-4400+

50Ω

DC to 4400 MHz SMA Male/Female

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	FF704
RoHS Status	Compliant
Environmental Ratings	ENV113

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

